


Hexalobular (6 Lobe) socket head cap screws with extremely low head

BN 9524



Additional information	Fasteners to the given specification have a reduced loadability due to the head geometry according to ISO 898-1.
Headform	Cylindrical extremely low
Drive	Hexalobular socket
Thread	fully threaded
Material	Steel
Property class	08.8
Surface	zinc plated blue

Article no.	d1	L	d2	k max.	a max.	Hexalobular socket	t max.	A~
3555988	M2	4	4	1,27	1,2	X5	0,9	1,5
3555989	M2	5	4	1,27	1,2	X5	0,9	1,5
3555990	M2	6	4	1,27	1,2	X5	0,9	1,5
3555991	M2	8	4	1,27	1,2	X5	0,9	1,5
3555993	M2	10	4	1,27	1,2	X5	0,9	1,5
3555994	M2,5	4	5	1,37	1,35	X6	1	1,75
3555995	M2,5	5	5	1,37	1,35	X6	1	1,75
3555996	M2,5	6	5	1,37	1,35	X6	1	1,75
3555997	M2,5	8	5	1,37	1,35	X6	1	1,75
3555998	M2,5	10	5	1,37	1,35	X6	1	1,75
3556000	M2,5	12	5	1,37	1,35	X6	1	1,75
3645732	M2,5	16	5	1,37	1,35	X6	1	1,75
3645733	M2,5	20	5	1,37	1,35	X6	1	1,75
3645734	M3	4	6	1,37	1,5	X8	1,1	2,4
3271396	M3	5	6	1,37	1,5	X8	1,1	2,4
3271397	M3	6	6	1,37	1,5	X8	1,1	2,4

Article no.	d1	L	d2	k max.	a max.	Hexalobular socket	t max.	A~
3271398	M3	8	6	1,37	1,5	X8	1,1	2,4
3271399	M3	10	6	1,37	1,5	X8	1,1	2,4
3271400	M3	12	6	1,37	1,5	X8	1,1	2,4
3271401	M3	16	6	1,37	1,5	X8	1,1	2,4
3271402	M3	20	6	1,37	1,5	X8	1,1	2,4
3645737	M3	25	6	1,37	1,5	X8	1,1	2,4
3645738	M3	30	6	1,37	1,5	X8	1,1	2,4
3271405	M4	5	8	1,5	1,6	X10	1,5	2,8
3060005	M4	6	8	1,5	1,6	X10	1,5	2,8
3060007	M4	8	8	1,5	1,6	X10	1,5	2,8
3060009	M4	10	8	1,5	1,6	X10	1,5	2,8
3271407	M4	12	8	1,5	1,6	X10	1,5	2,8
3271408	M4	16	8	1,5	1,6	X10	1,5	2,8
3271409	M4	20	8	1,5	1,6	X10	1,5	2,8
3645739	M4	25	8	1,5	1,6	X10	1,5	2,8
3645740	M4	30	8	1,5	1,6	X10	1,5	2,8
3060010	M5	6	9	1,5	2	X15	1,8	3,35
3060012	M5	8	9	1,5	2	X15	1,8	3,35
3060013	M5	10	9	1,5	2	X15	1,8	3,35
3060014	M5	12	9	1,5	2	X15	1,8	3,35
3060015	M5	16	9	1,5	2	X15	1,8	3,35
3271411	M5	20	9	1,5	2	X15	1,8	3,35
3271412	M5	25	9	1,5	2	X15	1,8	3,35
3645741	M5	30	9	1,5	2	X15	1,8	3,35
3645742	M6	6	10	1,5	2,5	X20	2,1	3,95
3060016	M6	8	10	1,5	2,5	X20	2,1	3,95
3060017	M6	10	10	1,5	2,5	X20	2,1	3,95
3060018	M6	12	10	1,5	2,5	X20	2,1	3,95
3060019	M6	16	10	1,5	2,5	X20	2,1	3,95
3060021	M6	20	10	1,5	2,5	X20	2,1	3,95
3271413	M6	25	10	1,5	2,5	X20	2,1	3,95
3271414	M6	30	10	1,5	2,5	X20	2,1	3,95
3645743	M6	35	10	1,5	2,5	X20	2,1	3,95
3645744	M6	40	10	1,5	2,5	X20	2,1	3,95
3060022	M8	8	13	1,5	3	X25	2,4	4,5
3060023	M8	10	13	1,5	3	X25	2,4	4,5
3060024	M8	12	13	1,5	3	X25	2,4	4,5
3060026	M8	16	13	1,5	3	X25	2,4	4,5
3060028	M8	20	13	1,5	3	X25	2,4	4,5
3271415	M8	25	13	1,5	3	X25	2,4	4,5
3271416	M8	30	13	1,5	3	X25	2,4	4,5
3271417	M10	10	16	1,5	3,5	X30	2,7	5,6
3271418	M10	12	16	1,5	3,5	X30	2,7	5,6
3271419	M10	16	16	1,5	3,5	X30	2,7	5,6
3271420	M10	20	16	1,5	3,5	X30	2,7	5,6
3271421	M10	25	16	1,5	3,5	X30	2,7	5,6
3271422	M10	30	16	1,5	3,5	X30	2,7	5,6