


Technical data sheet

Cone cable gland, PG thread, small cutting ring,
nickel-plated
Item no. 2082292



Cable gland with hexagonal intermediate connector, shape C4, to DIN 46320 with Pg connection thread to DIN 40430.
Pressure rings made of electrogalvanised and transparently passivated steel.
NR/SBR sealing ring.
Protection rating: with connection thread sealing ring IP 65, without connection thread sealing ring IP 54.
With simple sealing ring, with small internal diameter.
* Prices according to DEL notation.

CE IP 54 IP 65 Pg

CuZn	Brass
N	Nickel-plated

Master data


Item no.	2082292
Type	163 MS PG29
Description 1	Cable gland
Dimension	PG29
Material	Brass
Material symbol	CuZn
Surface	Nickel-plated
Surface symbol	N
Smallest sales unit (VG)	10,00 Piece
Weight	8,21 kg/100 pc.

Technical data sheet

Cone cable gland, PG thread, small cutting ring,
nickel-plated
Item no. 2082292



Technical data



Dimension E	43,50 mm
Dimension L	24,00 mm
Dimension L max.	24,00 mm
Dimension L1	8,00 mm
Dimension L2	16,50 mm
Dimension L3	4,00 mm
SW 1	40,00 mm
SW 2	37,00 mm
Type of seal	Sealing ring
Bend protection	☐
Sealing range D	24,00 - 26,00 mm
explosion-proof	☐
Flat cable threaded connection	☐
For Ex zone	Without
Thread	Pg 29
Thread type	PG
Thread length	8,00 mm
Fibre-glass reinforced	☐
Halogen-free	☐
Multiple sealing insert	☐
With locknut	☐
Impact-resistant	☐
Protection rating	IP54
Strain relief option	☐