


Junction box

WKE 4 - 8 x 1,5²



WKE 4 - 8 x 1,5²

Junction box

Productnumber: 86850801

Dimensions: 150 x 150 x 85 mm

Junction box, with protection class IP66, $U_i=450V$ AC, certified according to VDE (DIN EN 60670-1/-22 (VDE 0606-1/-22)), UL-EU (EN 62208), Push-out membranes, M20/M25/M32, (2 Rear, 12 Side), External fastening points, with E30 - E 90 electrical functional integrity according to DIN 4102 Part 12. Halogen-free enclosure made of special thermoplastic, terminals made of high-temperature-resistant special ceramic, universally positionable terminal holder

orange, Connection box, 8-pole, 0.5 - 2.5 mm², junction box 8-pole 0.5 - 1.5 mm², number of clampable conductors per pole:
8 x 0.5² / 4 x 0.75² / 6 x 1² / 6 x 1.5² / 2 x 2.5²

Accessories supplied:

Cover retainer, screw anchor, 3 off double membrane seals IP66 M20 sealing area 7 - 13 mm, 2 off double membrane seals IP66 M25 sealing area 9 - 17 mm, 1 off double membrane seal IP66 M32/4 sealing area 4 x 3.5-6 mm



Technical Data

electrical characteristics

Rated insulation voltage AC:	450 V
Rated insulation voltage DC:	450 V
max. wire cross section (wire branching):	1,5 mm²
Max. conductor cross section:	2,5 mm²
Min. conductor cross section:	0,5 mm²
Min. conductor cross section:	0,5 mm²
Protection class:	II
Type of protection:	IP66
secured junction:	no
Circuit integrity class:	E30/E60/E90
Number of poles (T-piece):	8
Number of poles (feed-through):	8
UL Type Rating:	other
Number of fuses in T-piece:	0

Colours

Base unit colour:	orange
Cover colour:	orange

Additional features

Range of application:	Communication wires
-----------------------	---------------------

Dimensions

Width:	150 mm
Length:	150 mm
Height:	85 mm
Inner length:	137 mm
Inner width:	137 mm
Inner height:	67 mm

Material characteristics

suitable for exterior use:	yes
Industry quality:	yes
Halogen free:	yes
Flammability class according with UL94:	V0
Glow-wire flammability according to EN 60695-2-11:	960 °C

mechanical properties

Type of fastening:	Wall/ceiling mounting
Impact strength:	IK08
Sealable:	yes

Ambient conditions

max. relative humidity 25°C:	95 %
max. relative humidity 40°C:	50 %
Min. ambient temperature:	-35 °C
Max. ambient temperature:	80 °C
24h ambient temperature:	60 °C
Set-up location:	Indoors / sheltered outdoors

Material

Base unit material:	Polycarbonate
Cover material:	Polycarbonate
Sealing material:	Polyurethane
Cover screw material:	Stainless steel V2A

Certificates

Test mark:	VDE (DIN EN 60670-1/-22 (VDE 0606-1/-22))
Test mark:	UL-EU (EN 62208)

Accessories

[26062001 - DMS M20/or - Double-membrane seals](#)

[26062501 - DMS M25/or - Double-membrane seals](#)

[26063201 - DMS M32/or - Double-membrane seals](#)

[26063301 - DMS M32/4 or - Double-membrane seals](#)

[22762001 - KVR M20-MGM/or - Cable gland](#)

[22762501 - KVR M25-MGM/or - Cable gland](#)

[22763201 - KVR M32-MGM/or - Cable gland](#)

[86310001 - WKE BK 1 - Mounting plate](#)

Cable gland

