



Clifford & Snell®

Yodalight® YL50 Hi-Vis

**Multi-purpose Audible & Visual
Signalling Device designed for use in
Fire, Commercial, Industrial & Marine
applications**

PRODUCT FEATURES

- Max sound output 112 dB(A) @ 1m
- IP66 rated as standard
- High Brightness LED Beacon
- 32 selectable tones meeting international regulations
- Flame retardant ABS enclosure
- Stainless steel fixings
- 2 stage alarm
- Independently selectable second stage option
- Lens available in eight colours
- Low current consumption



Product Approvals



Marine Equipment Directive MED
Regulations EN 54-3:2014 incl. A1:2019
IEC 60092-504:2016 IEC 60533:2015
Module B (BSI/MED/3.53/756093)
Module D (BSI/MED/PC/756095)



BS EN 54-3 : 2001 + A1:2002 + A2:2006
Type B
0086-CPR-774029



Merchant Shipping (Marine Equipment)
Regulations EN 54-3:2014 incl. A1:2019,
IEC 60092-504:2016, IEC 60533:2015
Module B (BSI/UK/3.53/738807)
Module D (BSI/UK/PC/738808)



BS EN 54-3 : 2001 + A1:2002 + A2:2006
Type B
KM 713890



EN 54-3 : 2001 + A1:2002 + A2:2006
Type B
2797-CPR-713892



Compliant

UK +44 (0) 121 446 5322 FR +33 (0) 170 721 271

✉ uksales@moflash.co.uk

exportsales@moflash.co.uk

KM-europ@moflash.com

🌐 www.moflash.com

Issue 4

TECHNICAL DATA

Electrical Data

Operating Voltage	Current Draw
24vDC ---	75mA at Tone 1
48vDC ---	116 mA
115vAC ~	65 mA
230vAC ~	55 mA

Ambient Conditions

Operating Temperatures	
Standard General	-35 °C to +70 °C
EN54 Pt:3 Fire	-25 °C to +55 °C
Storage Temperature	-40 °C to +70 °C
Max. Relative Humidity	93% ± 3 at 40 °C

Mounting / Installation

Devices should be mounted to a suitable flat wall or bulkhead avoiding any undue vibration and using the two lugs projecting from the case. The lugs are bored 8mm on 153mm centres. The minimum length of fixing screw required is 25mm. To maintain the IP rating of the enclosure, the cable entries must be fitted with a suitably rated cable gland (included). Max cable termination 2.5mm².

Mechanical Data

Enclosure Material	ABS FR UL94 5VB
Lens Material	PC FR UV Stable UL94 HB
External Fixings	Stainless Steel
Degree of Protection	IP66 (IEC60529)

Acoustic Data

Maximum Volume Output	112dB (A)
Volume Control Adjustment	-18 dB (A)
2 Stage Alarm with predetermined second stage as standard.	
Selectable second stage option available (DC units only) (2)	

Luminous Characteristics

Array Type	24vDC --- (*)	12 High Brightness LEDs
	48vDC --- (**)	25 High Brightness LEDs
	115vAC ~ (**)	25 High Brightness LEDs
	230vAC ~ (**)	25 High Brightness LEDs
Flash Rate	(*) 60 FPM, (**) 60/120 FPM User selectable	

Line integrity on 24vDC systems

- For 3 wire 2 stage alarm system, monitor via reverse polarity.
- For 2 wire 2 stage alarm system, monitor via threshold, (applied voltage < 1v) an end-of-line (E.O.L) resistor is required for line monitoring and should have a minimum resistance of 3k3 Ohms and 0.5 Watts, wire-wound or metal film type.

Standard Alarm Stage Options


Standard units offer a 2 stage alarm system with a predetermined second stage (see Tone Table on the Installation Sheet for details). A selectable second stage option is available for DC units only with the (2) prefix code in the selection table on page 3.

Additional Stage Alarm Options

Units with up to 8 independently selectable stages are available in a range of input voltages. However, these units do not carry any 3rd party approvals. Contact our technical department for further information.

Dimensional Drawing

We reserve the right to make alterations to the technical data, dimensions, weights, designs and products available without notice. The illustrations cannot be considered binding. All Dimensions in mm [inches] - Subject to alterations



SELECTION

Version	Enclosure Colour	Rated Operational Voltage	Lens Colour	Effective Candela (cd)	Order Number	Art. No.	Weight (kg)
YL50 Hi-Vis Sounder/LED combination BS EN 54 Pt:3 UKCA, CE, EU MED & UK MER	Red Flame (RF) RAL 2002	24vDC ---	Amber	9.22	YL50/DL/A/RF/HV/WR	245280	1.1
			Red	8.98	YL50/DL/R/RF/HV/WR	245281	1.1
			Green	27.52	YL50/DL/G/RF/HV/WR	245282	1.1
			Opal	10.87	YL50/DL/O/RF/HV/WR	245283	1.1
			Blue	8.18	YL50/DL/B/RF/HV/WR	245284	1.1
			Clear	29.21	YL50/DL/C/RF/HV/WR	245285	1.1
			Yellow	26.79	YL50/DL/Y/RF/HV/WR	245286	1.1
			Magenta	6.6	YL50/DL/M/RF/HV/WR	245287	1.1
		24vDC --- Independently Selectable 2 nd Stage Version	Amber	9.22	YL50/DL/A/RF/HV/WR(2)	245312	1.1
			Red	8.98	YL50/DL/R/RF/HV/WR(2)	245313	1.1
			Green	27.52	YL50/DL/G/RF/HV/WR(2)	245314	1.1
			Opal	10.87	YL50/DL/O/RF/HV/WR(2)	245315	1.1
			Blue	8.18	YL50/DL/B/RF/HV/WR(2)	245316	1.1
			Clear	29.21	YL50/DL/C/RF/HV/WR(2)	245317	1.1
			Yellow	26.79	YL50/DL/Y/RF/HV/WR(2)	245318	1.1
			Magenta	6.6	YL50/DL/M/RF/HV/WR(2)	245319	1.1
		48vDC ---	Amber	62.31	YL50/FL/A/RF/HV/WR	245288	1.1
			Red	55.12	YL50/FL/R/RF/HV/WR	245289	1.1
			Green	69.23	YL50/FL/G/RF/HV/WR	245290	1.1
			Opal	33	YL50/FL/O/RF/HV/WR	245291	1.1
			Blue	10.27	YL50/FL/B/RF/HV/WR	245292	1.1
			Clear	78.97	YL50/FL/C/RF/HV/WR	245293	1.1
			Yellow	66.83	YL50/FL/Y/RF/HV/WR	245294	1.1
			Magenta	19.12	YL50/FL/M/RF/HV/WR	245295	1.1
		115vAC ~	Amber	62.31	YL50/LL/A/RF/HV/WR	245296	1.18
			Red	55.12	YL50/LL/R/RF/HV/WR	245297	1.18
			Green	69.23	YL50/LL/G/RF/HV/WR	245298	1.18
			Opal	33	YL50/LL/O/RF/HV/WR	245299	1.18
			Blue	10.27	YL50/LL/B/RF/HV/WR	245300	1.18
			Clear	78.97	YL50/LL/C/RF/HV/WR	245301	1.18
			Yellow	66.83	YL50/LL/Y/RF/HV/WR	245302	1.18
			Magenta	19.12	YL50/LL/M/RF/HV/WR	245303	1.18
		230vAC ~	Amber	62.31	YL50/NL/A/RF/HV/WR	245304	1.18
			Red	55.12	YL50/NL/R/RF/HV/WR	245305	1.18
			Green	69.23	YL50/NL/G/RF/HV/WR	245306	1.18
			Opal	33	YL50/NL/O/RF/HV/WR	245307	1.18
			Blue	10.27	YL50/NL/B/RF/HV/WR	245308	1.18
			Clear	78.97	YL50/NL/C/RF/HV/WR	245309	1.18
			Yellow	66.83	YL50/NL/Y/RF/HV/WR	245310	1.18
			Magenta	19.12	YL50/NL/M/RF/HV/WR	245311	1.18