

## Torque screwdriver set TorqueVario®-S ESD



### 0,4-1,0 Nm assorted, variably adjustable torque limit, 14-pcs. incl. box

2882S13

| Order-No. |                                                                            |
|-----------|----------------------------------------------------------------------------|
| 43898     | 1                                                                          |
| ○         | 1 x Torque screwdriver TorqueVario®-S ESD variably adjustable torque limit |
| ○         | 1 x Bit holder clamping with ball for torque screwdriver with long handle  |
|           | 1 x Setting tool for torque screwdriver with long handle                   |
| ⊕         | 1 x PH0 / 1 x PH1                                                          |
| ⊕         | 1 x PZ0 / 1 x PZ1                                                          |
| ⊕         | 1 x T4 / 1 x T5 / 1 x T6 / 1 x T8                                          |
|           | 1 x Box                                                                    |

DIN EN ISO 6789.  
IEC 61340-5-1.

## Torque screwdriver TorqueVario®-S ESD




### variably adjustable torque limit

2882

| Order-No. | Nm           | ±6%  | ⊕   | ⊕   | ⊕  | ⊕ |
|-----------|--------------|------|-----|-----|----|---|
| 36851     | 0.04 - 0.46• | 10 % | 4.0 | 127 | 23 | 1 |
| 26865     | 0.1 - 0.6•   | 10 % | 4.0 | 127 | 23 | 1 |
| 36852     | 0.1 - 0.6•   | 6 %  | 4.0 | 127 | 23 | 1 |
| 26629     | 0.4 - 1•     | 6 %  | 4.0 | 127 | 23 | 1 |
| 26866     | 0.5 - 2•     | 6 %  | 4.0 | 131 | 30 | 1 |
| 30495     | 0.8 - 5•     | 6 %  | 4.0 | 138 | 36 | 1 |

• Precision in range of 0.1-0.46 Nm.  
IEC 61340-5-1. DIN EN ISO 6789.

### INFOBOX: Electrostatic conductive ESD tools



- Dissipative tools by Wiha discharge the electrostatic energy in a controlled, safe manner.
- ESD tools meet the ESD Standard IEC 61340-5-1.