




- NOTES:
- 1.LCD TYPE: TFT
 - 2.LCD DISPLAY: Normally Black/Transmissive
 - 3.The tolerance unless classified ±0.3mm
 - 4. Component Area; Insulating Tape; Shading tape; :Kapton tape;
 - 5.CN1 connector : CviLux CI4406M1H00 (1.25pitch ; 6pin) or compatible
 - 6.CN2 connector : Starconn 300E40-0010RA-G3 (0.5pitch ; 40pin) or compatible

007				PART NO:	久正光電股份有限公司 POWERTIP TECHNOLOGY CORPORATION									
006				PH128800T006-ZFC	Design	Clare			(3)	Surface	Tolerance Length(Min) (mm) Precision Level	Precision Level		
005				DRAWING NAME :			Check	Tina	Unit	MM			Material	
004				LMD-PH128800T006-ZFC	Scale	1:1			Thickness	1 ~ 4 4 ~ 16 16 ~ 63 63 ~ 250 250 ~ 1000				
003				TITLE:	Approve	Bright	Page	1/1	Quantity					
002	Modify Dimension	Clare	2023/6/5	LCD MODULE DRAWING										
001	NEW DRAWING	Clare	2023/4/6											
REV	REV BY	REVISER	DATE											