

# Spring-loaded test probe

## GKS-075 291 064 A 2800 C

Item GKS-075-0150



**ingun**<sup>®</sup>  
Partner for Future Technology

- Well-established test probes for contacting PCBs
- For optimal contact to the test points (e.g. pads, vias, and pins), various tip styles with various diameters and finishes are available.
- Various spring forces available as well as versions with stainless steel springs suitable for high temperatures

### General data

|                                |                                               |
|--------------------------------|-----------------------------------------------|
| Product group                  | ICT / FCT (in-circuit test and function test) |
| Sub-product group              | Standard stroke test probe                    |
| Series                         | GKS-075                                       |
| Grid                           | 1.91 mm [75 mil]                              |
| Contacting from                | Pad, via                                      |
| Magnetic                       | Yes                                           |
| Installation type              | Plug-in                                       |
| Quick-exchange system          | Yes                                           |
| Adjustable installation height | No                                            |
| Non-rotating                   | No                                            |
| Compatible receptacle(s)       | KS-075                                        |
| Min. temperature               | - 100 °C [- 212 °F]                           |
| Max. temperature               | + 200 °C [+ 392 °F]                           |
| RoHS-compliant                 | RoHS-3;6a                                     |

### Electrical data


|                                       |           |
|---------------------------------------|-----------|
| Current load capacity / rated current | 3 A       |
| Typical resistance (Ri)               | <100 mOhm |

### Mechanical data

|                                |                   |
|--------------------------------|-------------------|
| Total length                   | 33.1 mm [1.30 in] |
| Barrel diameter                | 1.02 mm [.040 in] |
| Maximum stroke                 | 6.35 mm [.25 in]  |
| Spring pre-load                | 0.65 N [2.33 ozf] |
| Collar height                  | 00                |
| Spring force at working stroke | 2.8 N [10.0 ozf]  |
| Recommended working stroke     | 4.3 mm [.169 in]  |

### Tip style data


|                    |                          |
|--------------------|--------------------------|
| Tip style          | 91 dagger, self-cleaning |
| Tip diameter       | 0.64 mm [.025 in]        |
| Tip style surface  | A gold                   |
| Tip style material | 2 steel                  |



Spring-loaded test probe  
**GKS-075 291 064 A 2800 C**  
Item GKS-075-0150



**ingun**<sup>®</sup>  
Partner for Future Technology



**INGUN Prüfmittelbau GmbH**

Max-Stromeyer-Straße 162  
78467, Constance, Germany  
Phone +49 7531 8105-0  
Customer hotline +49 7531 8105-888  
Fax +49 7531 8105-65  
info@ingun.com



Prices and delivery times on request.  
Technical changes reserved. 08/23 EN

Learn more about  
ICT/FCT Test probes



ICT/FCT TEST PROBES

ingun.com