




Application Tooling > Hand Crimping Tools



Tool Grade: **Premium Crimp Tooling**
Die Sets Type: **Removable/Interchangeable**
Specification Type: **MIL Spec, TE Product Specification (114-)**
TE Certification: **Yes – Certificate Included**
Power Technology Type: **Battery, Hydraulic, Manual**

Features

Other

Crimp Form-Wire Barrel Type	Closed Barrel - Confined Crescent
Tool Grade	Premium Crimp Tooling
Die Sets Type	Removable/Interchangeable
Specification Type	MIL Spec, TE Product Specification (114-)
TE Certification	Yes – Certificate Included
Power Technology Type	Battery, Hydraulic, Manual
Tooling Type	Die Assembly

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC



Free

Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 59974-1 HYP8 8-2AWG MANUAL TOOL-No Dies	TE Part # 52042-3 TERMINAL,R PG 6 1/4	TE Part # 52264-1 TERMINAL R PG 6 3/8	TE Part # 52264 TERMINAL R PG 6 5/16
TE Part # 52042-1 TERMINAL,R PG 6 1/4	TE Part # 52265 TERMINAL R PG 6 10	TE Part # 52042-2 TERMINAL,R PG 6 8	TE Part # 52042 TERMINAL,R PG 6 8
TE Part # 52350 TERMINAL R PG 6 1/2	TE Part # 69051 HYP8 8-2AWG 8T HEAD	TE Part # 55679-1 TERMINAL,R PG 6 1/4	TE Part # 324659 SPLICE BUTT M-M TERMINYL 6






TE Part # 53946-1
TERMINAL,R PVF2 PG 6 1/4



TE Part # 54947-1
TERMINAL,R PVF2 PG 8 5/16

Customers Also Bought



TE Part #48757-1
HYP8/10 PLASTI-GRIP/10 2/0AWG DIE SET



TE Part #ZPF000000000032921
983-ORS 18-31 S9 L



TE Part #ZPF000000000033047
983-ORS 22-19 SN-L



TE Part #ZPF000000000099647
983-ORS 28-06 SY-L-A1325



TE Part #ZPF000000000036309
983-6RS 20-41 S6 L



TE Part #ZPF000000000099640
983-6RS 28-06 P8 L-A1325

TE Part #ZPF000000000100628
161-8006-00

TE Part #ZPF000000000002079
200-1332-16

TE Part #ZPF000000000099639
983-6RS 28-06 P7 L-A1325

TE Part #800383-000
CTA-0078

Documents

Product Drawings
HYP8 PLASTI-GRIP 6AWG 69051 DIE SET
English

Datasheets & Catalog Pages
AT-Hydraulic Crimp Tooling Solutions-1654519
English

Bottoming Dies
English



Instruction Sheets

Instruction Sheet (U.S.)

English

Instruction Sheet (U.S.)

English