

Alustyle | End cover



ASD 1030-7024

Order no.: 94422100

For ASP... 1030

* = Available on request.

Characteristics

Colour of enclosure group

Graphite grey, similar to RAL 7024

Enclosure Material

Extruded profiles: Al Mg Si 0.5 powder-coated;
Diecast lid: zinc alloy Z410 / aluminium GD Al Si 12 (ASD 1540), powder-coated;
Seal: TPE;
for details see Technical Information

Scope of delivery

Lid including dark grey seal, screws, graphite grey screw covers

Note


max. achievable ingress protection IP 66 / IP 68 – 1.2m (2 hrs.) (dependent on profile version)

Important!


To compensate for pressure when temperatures change and cause moisture in the enclosure, we recommend that you use a **pressure compensation** element.

10.08.2023

Product drawing



Enclosure concept



In order to ensure that you can determine **the correct quantity of elements for your application**, we are providing you here with a DAE calculator.

» [Additional information](#)

Technical documentation / Downloads

Technical drawings

3D product data in STEP format:

Login to download

Drawing for mechanical processing:

94422100 ASD-1030-7024-G.dxf

(778.4 KB)

Milling contours are shown here as a DXF file. (Sub D, USB, HDMI, cable glands, ...)

Product drawing in PDF format:

94422100 ASD-1030-7024.pdf

(147.9 KB)

Product drawing in DXF format:

94422100 ASD-1030-7024.dxf

(1.0 MB)

Works test certificates

686 WPZ-Alustyle-ASP DE.pdf

(179.3 KB)

686 WPZ-Alustyle-ASP EN.pdf

(151.6 KB)

691 WPZ-Alustyle-ASPH DE.pdf

(191.3 KB)

691 WPZ-Alustyle-ASPH EN.pdf

(183.5 KB)

Product information

alustyle en.pdf

(1.5 MB)