

Technical data sheet

Cable gland, metric thread, UV-resistant, light grey

Item no. 2022906



Cable gland with metric connection thread in cap nut design, suitable for junction boxes, housings, distributor cabinets in private and industrial areas. With strain relief and integrated sealing lip, tested according to DIN EN 62444. Protection class IP68. Can be used between -20°C and +65°C.




PA Polyamide

Master data

Item no.	2022906
Type	V-TEC VM50UV LGR
Description 1	Cable gland
Description 2	UV-resistant
Dimension	M50
Colour	Light grey
Material	Polyamide
Material symbol	PA
Smallest sales unit (VG)	5 Piece
Weight	5,48 kg/100 pc.

Technical data



Dimension E	54,00 mm
Dimension L min.	43,00 mm
Dimension L max.	52,00 mm
Dimension L1	12,00 mm
Dimension L2	8,00 mm
WAF	54,00 mm
Version	Straight
Type of seal	Sealing ring
Bend protection	☐
Sealing range D	23,00 - 35,00 mm
explosion-proof	☐
Flat cable threaded connection	☐
For Ex zone	Without
For Ex zone gas	Without
For Ex zone dust	Without
Flame-resistant	acc. to VDE 0471/DIN 695 Part 2-1, test temperature 650°C
Thread	M50 x 1,5
Thread type	Metric
Thread length	12,00 mm
Nominal thread size	50
Fibre-glass reinforced	☐

Technical data sheet

Cable gland, metric thread, UV-resistant, light grey

Item no. 2022906



Technical data

Halogen-free	☒
Installation torque	12,00 Nm
Multiple sealing insert	☐
With locknut	☐
Impact-resistant	☐
Hexagonal corner dimension	54,00 mm
Protection rating	IP68
Splittable gland	☐
max. permitted ambient temperature	-20,00 - 65,00 °C
Strain relief option	☒