


Technical data sheet

Cone cable gland, PG thread, cutting ring, nickel-plated

Item no. 2082632



Cable gland with hexagonal intermediate connector, shape C4, to DIN 46320 with Pg connection thread to DIN 40430.

Pressure rings made of electrogalvanised and transparently passivated steel.

NR/SBR sealing ring.

Protection rating: with connection thread sealing ring IP 65, without connection thread sealing ring IP 54.

With cutting ring.

* Prices according to DEL notation.



CuZn	Brass
N	Nickel-plated

Master data

Item no.	2082632
Type	162 MS PG48
Description 1	Cable gland
Description 2	with cutting ring
Dimension	PG48
Material	Brass
Material symbol	CuZn
Surface	Nickel-plated
Surface symbol	N
Smallest sales unit (VG)	5,00 Piece
Weight	33,10 kg/100 pc.


Technical data sheet

Cone cable gland, PG thread, cutting ring, nickel-plated

Item no. 2082632



Technical data



Dimension E	69,00 mm
Dimension L	44,00 mm
Dimension L max.	44,00 mm
Dimension L1	10,00 mm
Dimension L2	23,00 mm
Dimension L3	6,00 mm
SW 1	64,00 mm
SW 2	60,00 mm
Type of seal	Cuttable sealing ring
Bend protection	☐
Sealing range D	36,00 - 47,00 mm
explosion-proof	☐
Flat cable threaded connection	☐
For Ex zone	Without
Thread	Pg 48
Thread type	PG
Thread length	10,00 mm
Fibre-glass reinforced	☐
Halogen-free	☐
Multiple sealing insert	☐
With locknut	☐
Impact-resistant	☐
Protection rating	IP54
max. permitted ambient temperature	-20,00 - 65,00 °C
Strain relief option	☐