

Technical data sheet

Expansion piece, metric thread

Item no. 2088283



The areas of application for brass cable glands range from junction boxes as a distribution/connection box up to large industrial applications for safe floor routing to switchgear cabinets with a control and distribution function. For high mechanical requirements, OBO can offer the entire family of extensions (Part K) to DIN 46320.

* Prices according to DEL notation.

CE M

CuZn	Brass
N	Nickel-plated

Master data

Item no.	2088283
Type	165 ADA M25-32
Description 1	Extension
Description 2	M - M
Dimension	M25-M32
Material	Brass
Material symbol	CuZn
Surface	Nickel-plated
Surface symbol	N
Smallest sales unit (VG)	50,00 Piece
Weight	2,71 kg/100 pc.


Technical data sheet

Expansion piece, metric thread



Item no. 2088283

Technical data



Dimension D	20,80 mm
Dimension E	35,80 mm
Dimension L	20,70 mm
Dimension L1	7,40 mm
Dimension L2	8,00 mm
WAF	34,00 mm
explosion-proof	☐
Thread	M25-M32
Thread type: External thread	Metric
Thread type: Internal thread	Metric
External thread	M25
Thread dimension, metric, external	25,00
Internal thread	M32
Thread dimension, metric, internal	32,00
Nickel-plated	☒