

# LED Filament B2C – G45\_ Red glass

Authorized Licensee for TOSHIBA trademark



## 1. Specification:

### A. General Data

|                                           |                                 |
|-------------------------------------------|---------------------------------|
| Model                                     | G45 filament 4.5W E14 Red glass |
| P/N                                       | DELS-FGR44P5R4AF11              |
| Westnet Code                              | 00172732                        |
| Rated Voltage                             | 230 VAC                         |
| Frequency                                 | 50 Hz                           |
| Rated Wattage                             | 4.5 W                           |
| Deviation Tolerance of Wattage            | ±10 %                           |
| Rated Current                             | 0.039 A                         |
| Maximum Input Current                     | 0.045 A                         |
| Start On                                  | <0.5S                           |
| Warm up time                              | <1S                             |
| Dimmable                                  | NO                              |
| Beam Angle                                | 270°                            |
| Energy Efficiency Class(EEC) <sup>®</sup> | Not applicable                  |
| Peak luminous intensity (cd)              | Non-directional                 |
| R9 CRI                                    | Not applicable                  |
| Survival factor                           | 0.9                             |
| Lumen Maintenance factor                  | 93.1%                           |
| Safety requirements                       | CE                              |
| Displacement factor (cos φ1)**            | No limit                        |

|                                  |                                                              |
|----------------------------------|--------------------------------------------------------------|
| Stroboscopic effect metric (SVM) | 0.9                                                          |
| Flicker metric (PstLM)           | 1                                                            |
| Applicable Environments          | Dry locations;<br>Not suitable for totally enclosed fixtures |
| Ingress protection rating        | IP20                                                         |
| Impact resistance                | N.A                                                          |
| Incandescent Equivalent          | 40W                                                          |
| Base                             | E14                                                          |
| Photobiological Group            | RG 1                                                         |

\* Displacement factor tolerance +/- 10%

\*\*No limit at  $P_{on} \leq 5W$

⦿ The product is excepted from Commission Delegated Regulation (EU) 2019/2015 on the energy labelling of light sources

#### B. Light Data

|                                   |                |
|-----------------------------------|----------------|
| Color                             | Red light      |
| Color Temperature (CCT)           | Not applicable |
| Lumen Output<br>( $\phi$ Total °) | Not applicable |
| Color Rendering Index             | Not applicable |
| Efficacy( $\phi$ Total °)         | Not applicable |
| Color Consistency                 | Not applicable |

#### C. Lifetime

(Supplied Voltage: AC 230V ; Ambient Temperature: 25°C)

|                              |                           |
|------------------------------|---------------------------|
| Lumen Maintenance Factor     | 70% of the rated lifetime |
| Rated Lifetime – $L_{70B50}$ | 15,000 hrs                |
| Switch cycles                | >20,000                   |

#### D. Temperature Operation

|                              |              |
|------------------------------|--------------|
| Normal operation temperature | -20°C ~ 40°C |
| Relative Humidity            | 10% ~ 90%    |


#### E. Geometric Data

|                        |                                 |
|------------------------|---------------------------------|
| Model                  | G45 filament 4.5W E14 Red glass |
| Maximum overall length | 45 ± 2 mm                       |
| Maximum overall width  | 80 ± 2 mm                       |

## F. Environmental relevant materials

## 2. Outline Drawing

Unit : mm




## Material Information

1. Globe & Body : Glass
2. Base : Metal


### 3. Light Distribution Curve

FWHM 270°



### 4. Spectrum Distribution

- Red light



## 5. Warnings

Before replacing, turn off power and let lamp cool to avoid electrical shock or burn.

## 6. Cautions

Only to apply in dry and most of open fixtures with lamp-holders that offer sufficient space (10 mm free air space). Not intended for use with emergency light fixtures for exit lights.

## 7. Notes

All characteristics are estimated at room temperature (25°C), free air burning, base up burning position and at rated voltage. In view of the complex manufacturing process for light above for the technical LED parameters are merely statistical values that do not necessarily correspond to the actual technic individual products may vary from the typical values.

## 8. Logistic information

|                                  |                                 |
|----------------------------------|---------------------------------|
| <b>Model</b>                     | G45 filament 4.5W E14 Red light |
| <b>Pieces per pack</b>           | 1                               |
| <b>EAN code on pack</b>          | 4711112386888                   |
| <b>Size of pack</b>              | 50 * 50 * 95mm                  |
| <b>Weight per pack (G.W)</b>     | 42g                             |
| <b>Packs per inner box</b>       | N/A                             |
| <b>EAN code on inner box</b>     | N/A                             |
| <b>ITF code on inner box</b>     | N/A                             |
| <b>Size of inner box</b>         | N/A                             |
| <b>Weight per inner box(G.W)</b> | N/A                             |
| <b>Packs per outer box</b>       | 100                             |
| <b>EAN code on outer box</b>     | N/A                             |
| <b>ITF code on outer box</b>     | 14711112386885                  |
| <b>Size of outer box</b>         | 560 * 275 * 220mm               |

|                           |                                                                                    |
|---------------------------|------------------------------------------------------------------------------------|
| Weight per outer box(G.W) | 3.3g                                                                               |
| Packing Photograph        |  |

## 9. ERP Label

N/A

## 10. Conformity

|                                            |                                                                                                     |
|--------------------------------------------|-----------------------------------------------------------------------------------------------------|
| 2014/35/EU;<br>Low Voltage<br>Directive    | EN 62560:2012 + A11:2019 、 EN 62493:2015 、 EN 62471:2008<br>IEC TR 62778:2014                       |
| 2014/30/EU;<br>EMC Directive               | EN IEC 55015:2019 + A11:2020 、 EN IEC 61000-3-2:2019 、 EN 61547:2009<br>EN 61000-3-3:2013 + A1:2019 |
| 2009/125/EC;<br>ErP Directive              | (EU) 2019/2015 、 (EU) 2019/2020 、 (EU)2021/340 、 (EU)2021/341                                       |
| 2011/65/EU+(EU)2015/863;<br>RoHS Directive | EN 50581: 2012                                                                                      |

