

Spring-loaded test probe

GKS-103 105 230 A 1502

Item GKS-103-0031



GO TO PRODUCT

ingun[®]

Partner for Future Technology

General data

Product group	ICT / FCT (in-circuit test and function test)
Sub-product group	Metric standard
Series	GKS-103
Grid	4.5 mm [177 mil]
Contacting from	Pad, Female connector
Magnetic	Yes
Installation type	Plug-in
Quick-exchange system	Yes
Adjustable installation height	No
Non-rotating	No
Compatible receptacle(s)	KS-103, KS-103 23
Min. temperature	- 40 °C [- 104 °F]
Max. temperature	+ 80 °C [+ 176 °F]
RoHS-compliant	RoHS-3;6c

Electrical data


Current load capacity / rated current	5 A
Typical resistance (Ri)	<30 mOhm

Mechanical data

Total length	29.3 mm [1.15 in]
Barrel diameter	3 mm [.118 in]
Maximum stroke	6 mm [.236 in]
Spring pre-load	0.44 N [1.58 ozf]
Collar height	.02
Spring force at working stroke	1.5 N [5.39 ozf]
Recommended working stroke	4.8 mm [.188 in]

Tip style data

Tip style	05 bullet-nosed (full radius)
Tip diameter	2.3 mm [.090 in]
Tip style surface	A gold
Tip style material	1 brass



Spring-loaded test probe


GKS-103 105 230 A 1502

Item GKS-103-0031



ingun[®]

Partner for Future Technology



INGUN Prüfmittelbau GmbH

Max-Stromeyer-Straße 162
78467, Constance, Germany
Phone +49 7531 8105-0
Customer hotline +49 7531 8105-888
Fax +49 7531 8105-65
info@ingun.com



Prices and delivery times on request.
Technical changes reserved. 11/23 EN

Learn more about
ICT/FCT Test probes

