

Spring-loaded test probe

GKS-422 002 230 A 3005

Item GKS-422-0362



ingun[®]

Partner for Future Technology

- Robust test probes with distinctive collar (stop) on the barrel

General data

Product group	ICT / FCT (in-circuit test and function test)
Sub-product group	Metric standard
Series	GKS-422
Grid	2.54 mm [100 mil]
Contacting from	Pin, Post
Magnetic	Yes
Installation type	Plug-in
Quick-exchange system	Yes
Adjustable installation height	No
Non-rotating	No
Compatible receptacle(s)	KS-112
Min. temperature	- 40 °C [- 104 °F]
Max. temperature	+ 80 °C [+ 176 °F]
RoHS-compliant	RoHS-3;6c

Electrical data


Current load capacity / rated current	8 A
Typical resistance (Ri)	<20 mOhm

Mechanical data

Total length	39.2 mm [1.54 in]
Barrel diameter	1.66 mm [.065 in]
Maximum stroke	7.6 mm [.299 in]
Spring pre-load	0.71 N [2.55 ozf]
Collar height	05
Spring force at working stroke	3 N [10.7 ozf]
Recommended working stroke	6.4 mm [.251 in]

Tip style data

Tip style	002-1 flat, outer-ø insulated
Tip diameter	2.3 mm [.090 in]
Tip style surface	A gold
Tip style material	0 plastic



Spring-loaded test probe


GKS-422 002 230 A 3005

Item GKS-422-0362



ingun[®]

Partner for Future Technology



INGUN Prüfmittelbau GmbH

Max-Stromeyer-Straße 162
78467, Constance, Germany
Phone +49 7531 8105-0
Customer hotline +49 7531 8105-888
Fax +49 7531 8105-65
info@ingun.com



Prices and delivery times on request.
Technical changes reserved. 11/23 EN

Learn more about
ICT/FCT Test probes

