

Spring-loaded test probe GKS-100 225 150 A 4000 E

Item GKS-100-1236



GO TO PRODUCT

ingun[®]

Partner for Future Technology

General data

Product group	ICT / FCT (in-circuit test and function test)
Sub-product group	Standard stroke test probe
Series	GKS-100 E long version
Grid	2.54 mm [100 mil]
Contacting from	Pin, Post
Magnetic	Yes
Installation type	Plug-in
Quick-exchange system	Yes
Adjustable installation height	No
Non-rotating	No
Compatible receptacle(s)	KS-100
Min. temperature	- 40 °C [- 104 °F]
Max. temperature	+ 80 °C [+ 176 °F]
RoHS-compliant	RoHS-3;6a

Electrical data


Current load capacity / rated current	5 A
Typical resistance (Ri)	<20 mOhm

Mechanical data

Total length	38.4 mm [1.51 in]
Barrel diameter	1.37 mm [.053 in]
Maximum stroke	6.35 mm [.25 in]
Spring pre-load	1.31 N [4.71 ozf]
Collar height	00
Spring force at working stroke	4 N [14.3 ozf]
Recommended working stroke	4.3 mm [.169 in]

Tip style data

Tip style	25 6-point crown with middle point, self-cleaning
Tip diameter	1.5 mm [.059 in]
Tip style surface	A gold
Tip style material	2 steel




Spring-loaded test probe

GKS-100 225 150 A 4000 E

Item GKS-100-1236



ingun[®]
Partner for Future Technology



INGUN Prüfmittelbau GmbH

Max-Stromeyer-Straße 162
78467, Constance, Germany
Phone +49 7531 8105-0
Customer hotline +49 7531 8105-888
Fax +49 7531 8105-65
info@ingun.com



Prices and delivery times on request.
Technical changes reserved. 09/23 EN

Learn more about
ICT/FCT Test probes



ICT/FCT TEST PROBES

ingun.com