

Spring-loaded test probe GKS-503 303 400 A 1502 M

Item GKS-503-0096



ingun[®]

Partner for Future Technology

General data

Product group	Screw-in test probe
Sub-product group	Screw-in test probe
Series	GKS-503 M screw-in
Grid	4.5 mm [177 mil]
Contacting from	Pin, Post
Magnetic	Yes
Installation type	Screw-in
Quick-exchange system	No
Type of test probe connection	Plug
Adjustable installation height	No
Non-rotating	No
Continuous plunger	ø1,4 x 5,0
Screw-in torque	10 - 20 cNm [.885 - 1.77 lbf·in]
Compatible connector(s)	SE-503
Compatible receptacle(s)	KS-500 M
Min. temperature	- 40 °C [- 104 °F]
Max. temperature	+ 80 °C [+ 176 °F]
RoHS-compliant	RoHS-3;6c

Electrical data



Current load capacity / rated current	8 A
Current rating, connection on plunger	15 A
Typical resistance (Ri)	<30 mOhm
Typical resistance (Ri), connection on plunger	<10 mOhm

Mechanical data

Total length	38 mm [1.49 in]
Barrel diameter	3 mm [.118 in]
Maximum stroke	7 mm [.275 in]
Spring pre-load	0.45 N [1.61 ozf]
Collar height	.02
Spring force at working stroke	1.5 N [5.39 ozf]
Recommended working stroke	5.6 mm [.220 in]

Tip style data

Tip style	03 inverse cone
Tip diameter	4 mm [.157 in]
Tip style surface	A gold
Tip style material	3 CuBe





Spring-loaded test probe

GKS-503 303 400 A 1502 M

Item GKS-503-0096



ingun[®]
Partner for Future Technology



INGUN Prüfmittelbau GmbH

Max-Stromeyer-Straße 162
78467, Constance, Germany
Phone +49 7531 8105-0
Customer hotline +49 7531 8105-888
Fax +49 7531 8105-65
info@ingun.com



Prices and delivery times on request.
Technical changes reserved. 11/23 EN

Learn more about
Screw-in test probe



SCREW-IN TEST PROBE

ingun.com