

High-current probe HSS-118 317 200 A 3008

Item HSS-118-0324



ingun®

Partner for Future Technology

General data

Product group	High-current test probe
Sub-product group	Standard HSS (press-in)
Series	HSS-118
Grid	2.54 mm [100 mil]
Contacting from	Pad, Via, Female connector
Magnetic	Yes
Installation type	Plug-in
Quick-exchange system	Yes
Adjustable installation height	No
Non-rotating	No
Compatible receptacle(s)	KS-112
Min. temperature	- 100 °C [- 212 °F]
Max. temperature	+ 200 °C [+ 392 °F]
RoHS-compliant	RoHS-3;6c

Electrical data



Current load capacity / rated current	20 A
Typical resistance (Ri)	<10 mOhm

Mechanical data

Total length	38.3 mm [1.50 in]
Barrel diameter	1.66 mm [.065 in]
Maximum stroke	5.3 mm [.208 in]
Spring pre-load	1 N [3.59 ozf]
Collar height	.08
Spring force at working stroke	3 N [10.7 ozf]
Recommended working stroke	4 mm [.157 in]

Tip style data

Tip style	17 hexagonal pyramid with cutting edges, self-cleaning
Tip diameter	2 mm [.078 in]
Tip style surface	A gold
Tip style material	3 CuBe




HIGH-CURRENT TEST PROBE

High-current probe
HSS-118 317 200 A 3008
Item HSS-118-0324



ingun[®]
Partner for Future Technology



INGUN Prüfmittelbau GmbH

Max-Stromeyer-Straße 162
78467, Constance, Germany
Phone +49 7531 8105-0
Customer hotline +49 7531 8105-888
Fax +49 7531 8105-65
info@ingun.com



Prices and delivery times on request.
Technical changes reserved. 11/23 EN

Learn more about
High-current test probe



HIGH-CURRENT TEST PROBE

ingun.com