

Test plug PS-RJ10-004-F7,6

Item 17824




ingun[®]
Partner for Future Technology

- Precise, low-wear contacting of RJ plug connectors
- Outstanding service life: up to 250,000 cycles under optimal conditions.
- Reliable data transmission
- Installation via optional floating mount
- Signal transmission via original connector plug

General data

Product group	PS test plug
Series	PS
Sub-series	PS-RJ
Grid	14.5 mm [570 mil]
DUT / contact	RJ-10
Installation type	Plug-in
DUT interface gender	F signal conductor female / socket
Floating mount	Yes
Non-rotating	Yes
Continuous plunger	No
KS sub-series	PSA-F7,6
Width	7.6 mm [.299 in]
Height	8.4 mm [.330 in]
Min. temperature	- 80 °C [- 176 °F]
Max. temperature	+ 150 °C [+ 302 °F]
RoHS-compliant	RoHS-3



Outer conductor data

Outer conductor tip style diameter	7.6 mm [.299 in]
Exchangeable outer conductor	No

Inner conductor data

Inner conductor tip style material	3 CuBe
Inner conductor tip style surface	U unplated
Number of inner conductors	4 2 differential pair
Exchangeable inner conductor	No
Inner conductor max. current load capacity	1 A
Number of inner conductor poles	4

Electrical data

Impedance	100 Ohm
Dielectric strength	0.06 kV

Test plug

PS-RJ10-004-F7,6

Item 17824




ingun[®]
Partner for Future Technology

Mechanical data

Total length
Barrel diameter
Installation height without receptacle

42 mm [1.65 in]
7.6 mm [.299 in]
42 mm [1.65 in]



INGUN Prüfmittelbau GmbH

Max-Stromeyer-Straße 162
78467, Constance, Germany
Phone +49 7531 8105-0
Customer hotline +49 7531 8105-888
Fax +49 7531 8105-65
info@ingun.com



Prices and delivery times on request.
Technical changes reserved. 12/23 EN

Learn more about
Test probes

