

Spring-loaded test probe

GKS-102 201 100 A 3002 W

Item GKS-102-0003



ingun[®]

Partner for Future Technology

General data

Product group	ICT / FCT (in-circuit test and function test)
Sub-product group	Metric standard
Series	GKS-102 W
Grid	2.54 mm [100 mil]
Contacting from	Pad
Magnetic	Yes
Installation type	Plug-in
Quick-exchange system	No
Type of test probe connection	Wire-wrap
Adjustable installation height	No
Non-rotating	No
Compatible receptacle(s)	KS-102
Min. temperature	- 40 °C [- 104 °F]
Max. temperature	+ 80 °C [+ 176 °F]
RoHS-compliant	RoHS-3;6a;6c

Electrical data


Current load capacity / rated current	5 A
Typical resistance (Ri)	<20 mOhm

Mechanical data

Total length	42.5 mm [1.67 in]
Barrel diameter	2 mm [.078 in]
Maximum stroke	6.5 mm [.255 in]
Spring pre-load	0.88 N [3.16 ozf]
Collar height	02
Spring force at working stroke	3 N [10.7 ozf]
Recommended working stroke	4.8 mm [.188 in]

Tip style data

Tip style	01 30° needle tip, self-cleaning
Tip diameter	1 mm [.039 in]
Tip style surface	A gold
Tip style material	2 steel



Spring-loaded test probe


GKS-102 201 100 A 3002 W

Item GKS-102-0003



ingun[®]

Partner for Future Technology



INGUN Prüfmittelbau GmbH

Max-Stromeyer-Straße 162
78467, Constance, Germany
Phone +49 7531 8105-0
Customer hotline +49 7531 8105-888
Fax +49 7531 8105-65
info@ingun.com



Prices and delivery times on request.
Technical changes reserved. 10/23 EN

Learn more about
ICT/FCT Test probes

