

Data sheet Product PF 510



Sockets>Sockets for TO ... cases
Sockets for TO 5

Features

contact material:	CuZn-alloy
contact spring:	gold-plated
surface contact / contact sleeve:	• Ni+≥0.2µm Au • Ni+4...6µm Sn
inner contact spring material:	CuBe-alloy
no. of contacts:	10
inner contact spring surface:	Ni+0,75µm Au
plugability for circuit points:	• 0,22x0,25mm... 0,4x0,55mm • Ø0,4...0,56mm
insert depth:	2.5...3.6mm
insertion / drawing force:	• 1.8 N/1.4 N • 4 lamellas contact
shock resistance:	50 g
vibration resistance max.:	15 g
volume resistance:	10 mΩ
contact resistance:	4 mΩ
contact resistance after 1000 cycles:	7 mΩ
capacity between two adjacent contacts:	0,4 pF
nominal current:	1.5 A
nominal voltage:	60 V DC
insulating body material:	PA 4.6. GF
temperature range:	• -40°C... +163°C • (260°C/10 s)
class of inflammability:	UL 94 V-0
version:	for TO 5
for cases:	standard
contact type:	precision contacts


specific insulation
resistance:

$>10^7 \Omega \cdot m$

contact sleeve:

gold-plated

Technical Drawing



Fischer Elektronik GmbH & Co. KG
DEUTSCHLAND • GERMANY • ALLEMAGNE

Nottebohmstraße 28
58511 Lüdenscheid

Telefon +49 2351 435-0
Telefax +49 2351 45754

info@fischerelektronik.de
www.fischerelektronik.de