



Product: [83350E](#)

Electronic, 4 C #20 Str SPC, TFE Ins, OA SPC Brd, TFE Jkt, MIL-W-16878/4 (Type E)

[Request Sample](#)

Product Description

High Temperature Electronic, 4 Conductor 20AWG (19x32) Silver Plated Copper, TFE Insulation, Overall Silver Plated Copper Braid(85%) Shield, TFE Outer Jacket, MIL-W-16878/4 (Type E)

Technical Specifications

Product Overview

Suitable Applications:	MIL-W-16878/4 (Type E) Spec; Extreme High/Low Temperature Environments; up to 600V analog signals & voltage control
------------------------	---

Construction Details

Conductor				
Element	No. of Elements	Size	Stranding	Material
Conductor(s)	4	20 AWG	19x32	SC - Silvered Copper

Insulation				
Element	Material	Nom. Thickness	Nom. Insulation Diameter	Color Code
Conductor(s)	PTFE - Polytetrafluoroethylene	0.0105 in (0.267 mm)	0.059 in (1.5 mm)	White, Black, Red, Green

Outer Shield		
Shield Type	Material	Coverage
Braid	Silvered Copper (SC)	85%

Outer Jacket		
Material	Nom. Thickness	Nom. Diameter
PTFE - Polytetrafluoroethylene	0.011 in (0.28 mm)	0.183 in (4.65 mm)

Overall Cable Diameter (Nominal):	0.183 in (4.65 mm)
-----------------------------------	--------------------

Electrical Characteristics

Electricals				
Element	Nom. Conductor DCR	Nom. Capacitance Cond-to-Cond	Nom. Capacitance Cond-to-Other (Conds + Shield)	Max. Current
Conductor(s)	7.8 Ohm/1000ft	31.7 pF/ft (104 pF/m)	51 pF/ft (170 pF/m)	6.5 Amps per conductor @ 25°C

Voltage	
Voltage Rating	
600 V	

Mechanical Characteristics

Temperature	
UL Temperature	Operating
200°C	-65°C to +200°C

Bend Radius	
Stationary Min.	Installation Min.
1.83 in (46.5 mm)	1.83 in (46.5 mm)

Max. Pull Tension:	60 lbs (27 kg)
Bulk Cable Weight:	35 lbs/1000ft

Standards and Compliance

Sustainability:	CA Prop 65
CPR Compliance:	CPR Euroclass: Eca
NEMA Compliance:	NEMA HP3
Military Compliance:	MIL-W-16878/4 (Type E except stranding), (insulated conductors)
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
UK Regulation Compliance:	UKCA Mark
APAC Compliance:	China RoHS II (GB/T 26572-2011)

Product Notes

Notes:	Teflon® is a registered trademark of E. I. duPont de Nemours and Co. used under license by Belden, Inc. Notes: LENGTH 100 FT, TOLERANCE: EXACT, MAX # OF PIECES: 2, MIN LENGTH EACH PIECE: 25 FT, LENGTH 500 FT, TOLERANCE: EXACT, MAX # OF PIECES: 3, MIN LENGTH EACH PIECE: 25 FT LENGTH 1000 FT, TOLERANCE: EXACT, MAX # OF PIECES: 6, MIN LENGTH EACH PIECE: 25 FT
--------	--

History

Update and Revision:	Revision Number: 0.555 Revision Date: 07-10-2023
----------------------	--

Part Numbers

Variants

Item #	Color	Putup Type	Length	UPC	Footnote
83350E 009500	White			612825204442	E
83350E 009100	White	Reel	100 ft	612825204428	E
83350E 0091000	White	Reel	1,000 ft	612825204435	E

© 2024 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.