


890 x20 xx
890 480 55
890 480 68

EN 60947-5-1



310.890.012.0318_AB




© D





WERMA Signaltechnik GmbH + Co. KG
D-78604 Rietheim-Weilheim
Telefon +49 (0)7424 / 9557-0
Telefax +49 (0)7424 / 9557-44
info@werma.com
www.werma.com

⚠ DANGER


- Ⓓ Anschluss **ausschließlich** durch ausgebildete Elektro-Fachkräfte.
- ⒼⒸ Electrical connection is to be made by trained electrical specialists **only**.
- Ⓕ Le branchement doit **uniquement** être effectué par des professionnels.
- Ⓘ Il collegamento deve essere eseguito **solo** da elettricisti specializzati.
- Ⓔ La conexión **sólo** debe ser realizada por electricistas debidamente formados.
- Ⓐ A ligação deve ser feita **exclusivamente** por profissional elétrico especializado.
- Ⓓ De aansluiting mag **enkel** gebeuren door erkende vakmensen.
- Ⓒ Připojení smí **provádět** pouze kvalifikovaný personál.
- Ⓐ Podłączenie **wyłącznie** przez specjalistów-elektryków.
- Ⓕ Liittäminen kuuluu **ainoastaan** koulutettujen sähköalan ammattilaisten tehtäviin.
- Ⓐ Подключение проводится только специа-листом-электриком.
- Ⓐ Bağlantı **sadece** eğitimli elektrik teknisyenleri tarafından yapılmalıdır.
- Ⓒ 布线需由专业电工执行




⚠ DANGER








3 890




4	890	+	 975 890 33 975 890 34 975 890 35 975 890 37
---	-----	---	--



				
	A	B	A	B
	93 mm 3.66"	190 mm 7.48"	245 mm 9.65"	338 mm 13.31"
	251,2 mm 9.89"	348,2 mm 13.71 "	406,2 mm 15.87"	496,2 mm 19,54"
	409,4 mm 16.12"	506,4 mm 19.94 "	561,4 mm 22.10"	645,4 mm 25.76"
	567,6 mm 22.35 "	664,6 mm 26.17"	719,6 mm 28.33"	812,6 mm 31.99"




6a	890 x20 xx
----	------------




890 x20 55		890 x20 68	
12 V DC	24 V DC	115 V AC 50/60 Hz	230 V AC / 50 Hz
260 mA	140 mA	25 mA	35 mA

6b	RGY 890 480 xx
----	----------------



	890 480 55		890 480 68
	12 V DC	24 V DC	230 V AC / 50 Hz
	170 mA	70 mA	40 mA
			
	220 mA	80 mA	40 mA
	210 mA	150 mA	40 mA



310.890.012.0318_AB

© D

 **WERMA**