



Image may differ from product. See technical specification for details.

W 6007-2Z

Stainless steel deep groove ball bearing with integral sealing

Stainless steel single row deep groove ball bearing with seals or shields on both sides, provide greater chemical and corrosion resistance. As with deep groove ball bearings generally, they are particularly versatile, have low friction and are optimized for low noise and low vibration, which enables high rotational speeds. They accommodate radial and axial loads in both directions, are easy to mount, and require less maintenance than other bearing types. The integral sealing can significantly prolong bearing service life because it keeps lubricant in the bearings and contaminants out.

- Greater chemical and corrosion resistance
- Integral sealing prolongs bearing service life
- Typical benefits of single row deep groove ball bearings

Overview

Dimensions

Bore diameter	35 mm
Outside diameter	62 mm
Width	14 mm

Properties

Filling slots	Without
Number of rows	1
Locating feature, bearing outer ring	None
Bore type	Cylindrical
Cage	Sheet metal
Matched arrangement	No
Radial internal clearance	CN
Tolerance class	Normal
Material, bearing	Stainless steel
Coating	Without
Sealing	Shield on both sides
Sealing type	Non-contact
Lubricant	Grease
Relubrication feature	Without


Performance

Basic dynamic load rating	13.8 kN
Basic static load rating	10.2 kN
Reference speed	24 000 r/min
Limiting speed	12 000 r/min

Logistics


Product net weight	0.15 kg
eClass code	23-05-08-01
UNSPSC code	31171504

Technical specification



Dimensions

d	35 mm	Bore diameter
D	62 mm	Outside diameter
B	14 mm	Width
d ₁	≈ 44 mm	Shoulder diameter
d ₂	≈ 44 mm	Recess diameter
D ₂	≈ 57.05 mm	Recess diameter
h	10.1 mm	Depth of locating slot
b	8.5 mm	Width of locating slot
r ₀	2 mm	Corner radius of locating slot
r _{1,2}	min. 1 mm	Chamfer dimension



Abutment dimensions

d _a	min. 40 mm	Diameter of shaft abutment
d _a	max. 43.5 mm	Diameter of shaft abutment
D _a	max. 57.5 mm	Diameter of housing abutment
r _a	max. 1 mm	Radius of shaft or housing fillet

Calculation data

Basic dynamic load rating	C	13.8 kN
Basic static load rating	C ₀	10.2 kN
Fatigue load limit	P _u	0.44 kN
Reference speed		24 000 r/min
Limiting speed		12 000 r/min
Minimum load factor	k _r	0.03
Calculation factor	f ₀	14.9

Mass

Mass bearing	0.15 kg
--------------	---------

Tolerance class

Dimensional tolerances	Normal
Radial run-out	Normal