

# High-current probe

## HSS-120 306 230 A 1502

Item HSS-120-0032



**ingun**<sup>®</sup>  
Partner for Future Technology

- Trusted, robust high-current probes, optimally sized for current load capacity ratio
- Low resistance probe with Ri typical: < 10 mOhm
- Large selection of tip styles and spring forces for optimum contact with DUT
- Optimum adjustment of the stroke ratios in the test fixture: The test probe collar is available in different heights, which, in combination with the receptacles, allows a range of installation heights

**INGUN SELECTION**

### General data

|                                |                         |
|--------------------------------|-------------------------|
| Product group                  | High-current test probe |
| Sub-product group              | Standard HSS (press-in) |
| Series                         | HSS-120                 |
| Grid                           | 4 mm [157 mil]          |
| Contacting from                | Pin, Post, Flat contact |
| Magnetic                       | Yes                     |
| Installation type              | Plug-in                 |
| Quick-exchange system          | Yes                     |
| Adjustable installation height | No                      |
| Non-rotating                   | No                      |
| Compatible receptacle(s)       | KS-113, KS-113 23       |
| Min. temperature               | - 100 °C [- 212 °F]     |
| Max. temperature               | + 200 °C [+ 392 °F]     |
| RoHS-compliant                 | RoHS-3;6c               |

### Electrical data


|                                       |          |
|---------------------------------------|----------|
| Current load capacity / rated current | 30 A     |
| Typical resistance (Ri)               | <10 mOhm |

### Mechanical data

|                                |                   |
|--------------------------------|-------------------|
| Total length                   | 27.3 mm [1.07 in] |
| Barrel diameter                | 2.65 mm [.104 in] |
| Maximum stroke                 | 5.3 mm [.208 in]  |
| Spring pre-load                | 0.39 N [1.40 ozf] |
| Collar height                  | 02                |
| Spring force at working stroke | 1.5 N [5.39 ozf]  |
| Recommended working stroke     | 4 mm [.157 in]    |

### Tip style data

|                    |                  |
|--------------------|------------------|
| Tip style          | 06 serrated      |
| Tip diameter       | 2.3 mm [.090 in] |
| Tip style surface  | A gold           |
| Tip style material | 3 CuBe           |



HIGH-CURRENT TEST PROBE


# High-current probe

## HSS-120 306 230 A 1502

Item HSS-120-0032



**ingun**<sup>®</sup>  
Partner for Future Technology



### INGUN Prüfmittelbau GmbH

Max-Stromeyer-Straße 162  
78467, Constance, Germany  
Phone +49 7531 8105-0  
Customer hotline +49 7531 8105-888  
Fax +49 7531 8105-65  
info@ingun.com



Prices and delivery times on request.  
Technical changes reserved. 11/23 EN

Learn more about  
High-current test probe



HIGH-CURRENT TEST PROBE

ingun.com