

High-current probe HSS-120 303 300 A 1002 M

Item HSS-120-0218



GO TO PRODUCT

ingun[®]

Partner for Future Technology

- Trusted high-current probes, optimally sized for current load capacity ratio

General data

Product group	High-current test probe
Sub-product group	Standard HSS (screw-in)
Series	HSS-120 M screw-in
Grid	4 mm [157 mil]
Contacting from	Pin, Post
Magnetic	Yes
Installation type	Screw-in
Quick-exchange system	Yes
Adjustable installation height	No
Non-rotating	No
Screw-in torque	10 - 20 cNm [.885 - 1.77 lbf·in]
Compatible receptacle(s)	KS-113 M
Min. temperature	- 100 °C [- 212 °F]
Max. temperature	+ 200 °C [+ 392 °F]
RoHS-compliant	RoHS-3;6c

Electrical data


Current load capacity / rated current	5 A
Typical resistance (Ri)	<10 mOhm

Mechanical data


Total length	28.3 mm [1.11 in]
Barrel diameter	2.65 mm [.104 in]
Maximum stroke	5.3 mm [.208 in]
Spring pre-load	0.26 N [.935 ozf]
Collar height	02
Spring force at working stroke	1 N [3.59 ozf]
Recommended working stroke	4 mm [.157 in]

Tip style data

Tip style	03 inverse cone
Tip diameter	3 mm [.118 in]
Tip style surface	A gold
Tip style material	3 CuBe





1:1



High-current probe
HSS-120 303 300 A 1002 M
Item HSS-120-0218



ingun[®]
Partner for Future Technology



INGUN Prüfmittelbau GmbH

Max-Stromeyer-Straße 162
78467, Constance, Germany
Phone +49 7531 8105-0
Customer hotline +49 7531 8105-888
Fax +49 7531 8105-65
info@ingun.com



Prices and delivery times on request.
Technical changes reserved. 11/23 EN

Learn more about
Screw-in test probe



[ingun.com](https://www.ingun.com)

SCREW-IN TEST PROBE