



UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE IN METRIC.

Revised Details

Item.	Description	Date	by
△			



SCALE 10:1



[1P*(24AWG BC+PE)+(28AWG BC+PVC)*2C]+AL+D+PVC OD4.5MM		
Conductor A	Material	10/0.16mm BCX1P
Conductor B	Material	7/0.12mm BCX2C
Insulator	Material	PE+PVC
Braided	Material	64/0.12mm ALMG
Shield	Material	AL/FOIL
Drain Wire	Material	0.25mm CCS
Outer Jacket	OD	4.5mm
	COLOR	Black

WIRE TABLE

USB A MALE		USB A MALE	
1	_____	1	_____
2	_____	2	_____
3	_____	3	_____
4	_____	4	_____
Drain wire		Drain wire	

Notes:

- CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY
- USB CABLE 2.0 VERSION 24AWG COPPER, OUTER JACKET OD=4.5MM
- HOOD:MOLDING TYPE,BLACK IN COLOR
- AL FOIL MUST BE WRAP 360° AROUND THE INNER INSULATOR.
- CABLE ELECTRICAL TEST:
<1>. 100% OPEN SHORT & MISS WIRE TEST.

	DES.		Feb.21.23	MDL	
	CHK.				
	APPR.			PDT.TIT	POS-CCP-USB2-AMAM-6
GEMBIRD		SCL.	1:1	SPEC	24AWG
Unit: MM			Page 1	Pages	CATEGORY
					AUDIO VIDEO

4

5

6