




FOR 客户名称	APPROVED 客户确认签字	ATTN 销售负责人

PART NUMBER:Micro USB-04-△

"△"	CRUST MATERIAL
NO LETTER	AL ALLOY(SILVER)
BK	AL ALLOY(BLACK)
OTHER COLOR CAN BE CUSTOMIZED	

SPECIFICATIONS:

- OPERATING TEMPERATURE: $-25^{\circ}\text{C} \sim +55^{\circ}\text{C}$ (NO FREEZING, KEEP THE AIR FLOWING AROUND PUSHBUTTON).
- OPERATION HUMIDITY: 45% ~ 85% RH (NO CONDENSATION).
- TRANSMISSION RATE: $\geq 30\text{MB/s}$.
- HEAD PORT: Micro USB2.0 B TYPE FEMALE.
- BACK PORT: Micro USB2.0 B TYPE MALE.
- TORQUE: 0.6Nm Max. APPLIED TO NUT.
- GENERAL TOLERANCE: 0-18mm = ± 0.25 , 18-80mm = ± 0.52 .

MATERIALS:
1.BODY: AL ALLOY.

BRAND 品牌		红波按钮制造有限公司			
ONPOW 欧宝龙®		ONPOW PUSH BUTTON MANUFACTURE CO.,LTD.			
TITLE 名称	PANEL MOUNTING TYPE MICRO USB2.0 CONNECTOR			UNIT 单位	mm
DWG NO. 图号	Micro USB-04		SCALE 比例	1 : 1	SIZE 图纸
FILE NAME 档案名称	Micro金属 USB2.0.DWG	DRAWN 制图	HCP 2023/12/14	SHEET 张	1/1
				REV. 更改	1