




PART NUMBER:Power jack-01-△

"△"	CRUST MATERIAL
NO LETTER	AL ALLOY(SILVER)
BK	AL ALLOY(BLACK)
OTHER COLOR CAN BE CUSTOMIZED	

SPECIFICATIONS:
1.OPERATING TEMPERATURE: -25℃~ +55℃(NO FREEZING, KEEP THE AIR FLOWING AROUND PUSHBUTTON).
2.OPERATION HUMIDITY: 45~ 85%RH(NO CONDENSATION).
3.TORQUE: 0.6Nm Max. APPLIED TO NUT.
4.GENERAL TOLERANCE:0-18mm=±0.25, 18-80mm=±0.52.

MATERIALS:
1.BODY: AL ALLOY.

BRAND 品牌		红波按钮制造有限公司			
ONPOW 欧宝龙®		ONPOW PUSH BUTTON MANUFACTURE CO.,LTD.			
TITLE 名称	PANEL MOUNTING TYPE MICRO POWER JACK CONNECTOR			UNIT 单位	mm
DWG NO. 图号	Power jack-01		SCALE 比例	1 : 1	SIZE 图纸
FILE NAME 档案名称	Power jack-01金属	DRAWN 制图	HCP 2023/12/15	SHEET 张	1/1
	.DWG			REV. 更改	1