


IEC 62080



144 000 66

444 xx0 66

144 000 67

444 xx0 67

144 000 75


144 000 68

444 xx0 75

444 xx0 68



EAC






© D

WERMA®

WERMA Signaltechnik GmbH + Co. KG
 D-78604 Rietheim-Weilheim
 Telefon +49 (0)7424 / 9557-0
 Telefax +49 (0)7424 / 9557-44
 info@werma.com
 www.werma.com

**DANGER**

- DE Anschluss **ausschließlich** durch ausgebildete Elektro-Fachkräfte.
- GB Electrical connection is to be made by trained electrical specialists **only**.
- FR Le branchement doit **uniquement** être effectué par des professionnels.
- IT Il collegamento deve essere eseguito **solo** da elettricisti specializzati.
- ES La conexión **sólo** debe ser realizada por electricistas debidamente formados.
- PT A ligação deve ser feita **exclusivamente** por profissional elétrico especializado.
- NL De aansluiting mag **enkel** gebeuren door erkende vakmensen.
- CZ Připojení smí **provádět** pouze kvalifikovaný personál.
- PL Podłączenie **wyłącznie** przez specjalistów-elektryków.
- FI Liittäminen kuuluu **ainoastaan** koulutettujen sähköalan ammattilaisten tehtäviin.
- RU Подключение проводится только специа-листом-электриком.
- TR Bağlantı **sadece** eğitimli elektrik teknisyenleri tarafından yapılmalıdır.
- CN 布线需由专业电工执行



444 x10 xx

- DE Bei Epilepsie ungeeignet!
- GB Unsuitable for epilepsy sufferers.
- FR Ne convient pas aux personnes souffrant d'épilepsie.
- IT Inadatto per epilettici.
- ES Inadecuado para epilépticos.
- NL Niet geschikt voor epileptici.
- PT Não aconselhavel a pessoas que sofrem de Epilepsia.
- CZ Nevhodné pro epileptiky.
- PL Nie stosować przy zchorzeniu padaczki.
- FI Ei soveltu epileptikoille.
- RU Не подходит для страдающих эпилепсией.
- TR Epilepsi hastalığı olanların kullanmaması önerilir.
- CN 不适用于癫痫病患者



I (U)


	U		
144 000 75	24 V AC / DC	200 mA	-
144 000 66	48 V AC 50/60 Hz	140 mA	-
144 000 67	115 V AC 50/60 Hz	55 mA	-
144 000 68	230 V AC 50/60 Hz	30 mA	-
444 x00 75	24 V AC / DC	200 mA	60 mA
444 x00 66	48 V AC 50/60 Hz	140 mA	40 mA
444 x00 67	115 V AC 50/60 Hz	55 mA	30 mA
444 x00 68	230 V AC 50/60 Hz	30 mA	30 mA
444 x10 75	24 V AC / DC	200 mA	80 mA
444 x10 66	48 V AC 50/60 Hz	140 mA	45 mA
444 x10 67	115 V AC 50/60 Hz	55 mA	30 mA
444 x10 68	230 V AC 50/60 Hz	30 mA	30 mA




1

1a - 144, 444
1b - 144, 444


1a



1b



2



3

