



LGE3M14120Q

Silicon Carbide Power MOSFET





$V_{DS} = 1200\text{ V}$
 $I_D@25^\circ\text{C} = 152\text{ A}$
 $R_{DS(ON)} = 14\text{ m}\Omega$

Features

- High speed switching
- Very low switching losses
- High blocking voltage with low on-resistance
- Temperature independent turn-off switching losses
- Halogen free, RoHS compliant

Benefits

- Cooling effort reduction
- Efficiency improvement
- Reduced cooling requirements
- Increased power density
- Increased system switching frequency



Applications

- EV motor drive
- PV string inverters
- Solar power optimizer
- Switch mode power supplies

TO-247-4 Pin definition

Table 1 Key performance and package parameters

Type	V_{DS}	I_{DS} $(T_C=25^\circ\text{C},$ $R_{th(j-c,max)})$	$R_{DS(ON), typ}$ $(V_{GS} = 18\text{ V}, I_D = 100\text{ A},$ $T_J=25^\circ\text{C})$	$T_{j,max}$	Marking	Package
LGE3M14120Q	1200 V	152 A	14 m Ω	175 $^\circ\text{C}$	LGE3M14120Q	TO-247-4



LGE3M14120Q

Silicon Carbide Power MOSFET



1、Maximum ratings

Table 2 Maximum rating ($T_c = 25^\circ\text{C}$ unless otherwise specified)

Symbol	Parameter	Value	Unit	Test Conditions	Note
$V_{DS,max}$	Drain source voltage	1200	V	$V_{GS} = 0\text{ V}$, $I_D = 100\text{ }\mu\text{A}$	
$V_{GS,max}$	Gate source voltage	-8 /+22	V	Absolute maximum values	
V_{GSop}	Gate source voltage	-4 /+18	V	Recommended operational values	
I_D	Continuous drain current	152	A	$V_{GS} = 18\text{ V}$, $T_C = 25^\circ\text{C}$	Fig.19
		108		$V_{GS} = 18\text{ V}$, $T_C = 100^\circ\text{C}$	
$I_{D(pluse)}$	Pulsed drain current	340	A	Pulse width t_P limited by $T_{j,max}$	Fig.22
P_D	Power dissipation	625	W	$T_C = 25^\circ\text{C}$, $T_J = 175^\circ\text{C}$	Fig.20
T_J, T_{stg}	Operating Junction and storage temperature	-40 to +175	$^\circ\text{C}$		
T_L	Soldering temperature	260	$^\circ\text{C}$	1.6mm (0.063") from case for 10s	
T_M	Mounting torque	1	Nm	M3 or 6-32 screw	
		8.8	lbf-in		

2、Thermal characteristics

Table 3 Thermal characteristics¹

Symbol	Parameter	Value	Unit	Test Conditions	Note
$R_{th(j-c)}$	Thermal resistance from junction to case	0.24	$^\circ\text{C/W}$		Fig.21
$R_{th(j-a)}$	Thermal resistance from junction to ambient	33			

¹ Not subject to production test. Parameter verified by design/characterization.

3、Electrical characteristics

3.1 Static characteristics

Table 4 Static characteristics (Tc = 25°C unless otherwise specified)

Symbol	Parameter	Min.	Typ.	Max.	Unit	Test Conditions	Note
$V_{(BR)DSS}$	Drain-source breakdown voltage	1200	-	-	V	$V_{GS} = 0V, I_D = 100\mu A$	
$V_{GS(th)}$	Gate threshold voltage	2.3	2.8	4	V	$V_{DS} = V_{GS}, I_D = 28mA$	Fig.11
		-	2.0	-	V	$V_{DS} = V_{GS}, I_D = 28mA, T_J = 175^\circ C$	
I_{DSS}	Zero gate voltage drain current	-	1	100	μA	$V_{DS} = 1200V, V_{GS} = 0V$	
I_{GSS}	Gate source leakage current	-	-	100	nA	$V_{GS} = 18V, V_{DS} = 0V$	
$R_{DS(on)}$	Current drain-source on-state resistance	-	17	21	m Ω	$V_{GS} = 15V, I_D = 100A$	Fig.4,5,6
		-	28	-		$V_{GS} = 15V, I_D = 100A, T_J = 175^\circ C$	
		-	14	18		$V_{GS} = 18V, I_D = 100A$	
		-	27	-		$V_{GS} = 18V, I_D = 100A, T_J = 175^\circ C$	
gfs	Transconductance	-	71	-	S	$V_{DS} = 20V, I_D = 100A$	Fig.7
		-	63	-		$V_{DS} = 20V, I_D = 100A, T_J = 175^\circ C$	
$R_{g,int}$	Internal gate resistance	-	0.9	-	Ω	$V_{AC} = 25mV, f = 1MHz$	
V_{SD}	Diode forward voltage	-	4.0	-	V	$V_{GS} = -4V, I_{SD} = 50A$	Fig.8,9,10
		-	3.5	-		$V_{GS} = -4V, I_{SD} = 50A, T_J = 175^\circ C$	

3.2 Dynamic characteristics

Table 5 Dynamic characteristics (Tc = 25°C unless otherwise specified)

Symbol	Parameter	Min.	Typ.	Max.	Unit	Test Conditions	Note
C_{iss}	Input capacitance	-	5469	-	pF	$V_{DS} = 1000V, V_{GS} = 0V$ $T_J = 25^\circ C, V_{AC} = 25mV$ $f = 100KHz$	Fig.17,18
C_{oss}	Output capacitance	-	235	-			
C_{rss}	Reverse capacitance	-	17.5	-			
E_{oss}	Coss stored energy	-	150	-	μJ		Fig.16



Q_{gs}	Gate source charge	-	54	-	nC	$V_{DS} = 800V, V_{GS} = -4/+18V$ $I_D = 100A$	Fig.12
Q_{gd}	Gate drain charge	-	45	-			
Q_g	Gate charge	-	230	-			

3.3 Switching characteristics

Table 6 Dynamic characteristics($T_c = 25^\circ C$ unless otherwise specified)

Symbol	Parameter	Min.	Typ.	Max.	Unit	Test Conditions	Note
E _{on}	Turn on switching energy	-	812	-	μJ	V _{DS} = 800V, V _{GS} = -4/+18V I _D = 100A, R _g = 2.5Ω, L = 120uH	Fig.26
E _{off}	Turn off switching energy	-	383	-			
t _{d (on)}	Turn on delay time	-	19	-	ns		Fig.27, 28
t _r	Rise time	-	29	-			
t _{d (off)}	Turn off delay time	-	42	-			
t _f	Fall time	-	9.3	-			

Table 7 Body diode characteristics

Symbol	Parameter	Min.	Typ.	Max.	Unit	Test Conditions	Note
V_{SD}	Diode forward voltage	-	4.0	-	V	$V_{GS} = -4V, I_{SD} = 50A$	Fig.8,9, 10
		-	3.5	-	V	$V_{GS} = -4V, I_{SD} = 50A$ $T_J = 175^\circ C$	
I_S	Continuous diode forward current	-	152	-	A	$V_{GS} = -4V, T_c = 25^\circ C$	
t_{rr}	Reverse recovery time	-	66	-	nS	$V_R = 800V, V_{GS} = -4V$ $I_D = 100A$ $di/dt = 3000A/\mu S,$ $T_J = 175^\circ C$	
Q_{rr}	Reverse recovery charge	-	1830	-	nC		
I_{rrm}	Peak reverse recovery current	-	52	-	A		

Note : When using SiC Body Diode the maximum recommended $V_{GS} = -4V$

4、Electrical characteristic diagrams




Figure 1. Output characteristics $T_J = -40\text{ }^{\circ}\text{C}$




Figure 2. Output characteristics $T_J = 25\text{ }^{\circ}\text{C}$




Figure 3. Output characteristics $T_J = 175\text{ }^{\circ}\text{C}$




Figure 4. Normalized on-resistance vs. temperature




Figure 5. On-resistance vs. drain current




Figure 6. On-resistance vs. temperature for various gate voltage




Figure 7. Transfer characteristic for various junction temperatures




Figure 8. Body diode characteristic at $T_J = -40\text{ }^{\circ}\text{C}$




Figure 9. Body diode characteristic at $T = 25\text{ }^{\circ}\text{C}$




Figure 10. Body diode characteristic at $T = 175\text{ }^{\circ}\text{C}$




Figure 11. Threshold voltage vs. temperature




Figure 12. Gate charge characteristic




Figure 13. 3rd quadrant characteristic at $T_J = -40^\circ\text{C}$




Figure 14. 3rd quadrant characteristic at $T_J = 25^\circ\text{C}$




Figure 15. 3rd quadrant characteristic at $T_J = 175^\circ\text{C}$




Figure 16. Output capacitor stored energy




Figure 17. Capacitances vs. drain-source voltage (0 - 200V)




Figure 18. Capacitances vs. drain-source voltage (0 - 1200V)




Figure 19. Continuous drain current derating vs. case temperature




Figure 20. Maximum power dissipation derating vs. case temperature




Figure 21. Transient thermal impedance (junction - case)




Figure 22. Safe operating area




Figure 23. Clamped Inductive switching energy vs. drain current ($V_{DD} = 800\text{V}$)




Figure 24. Clamped inductive switching energy vs. drain current ($V_{DD} = 600\text{V}$)




Figure 25. Clamped inductive switching energy vs. $R_{G(\text{ext})}$




Figure 26. Clamped inductive switching energy vs. temperature





Figure 27. Switching times vs. $R_{G(\text{ext})}$

5、Package drawing (TO-247-4L)



SYMBOL	DIMENSIONS		
	MIN.	NOM.	MAX.
A	4.83	5.02	5.21
A1	2.29	2.41	2.54
A2	1.91	2.00	2.16
b'	1.07	1.20	1.28
b	1.07	1.20	1.33
b1	2.39	2.67	2.94
b2	2.39	2.67	2.84
b3	1.07	1.30	1.60
b4	1.07	1.30	1.50
b5	2.39	2.53	2.69
b6	2.39	2.53	2.64
c	0.55	0.60	0.68
c1	0.55	0.60	0.65
D	23.30	23.45	23.60
D1	16.25	16.55	17.65
D2	0.95	1.19	1.25
E	15.75	15.94	16.13
E1	13.10	14.02	14.15
E2	3.68	4.40	5.10
E3	1.00	1.45	1.90
E4	12.38	13.26	13.43
e	2.54 BSC		
e1	5.08 BSC		
L	17.31	17.57	17.82
L1	3.97	4.19	4.37
L2	2.35	2.50	2.65
ϕP	3.51	3.61	3.65
$\phi P1$	7.19 REF.		
Q	5.49	5.79	6.00
S	6.04	6.17	6.30



6、 Test conditions




Figure A. Definition of switching times




Figure B. Dynamic test circuit




Figure C. Definition of diode switching characteristics

Figure C. Definition of body diode switching characteristics