





EN 60598: 890 X00 00, 890 X10 00,
895 X00 00, 895 X10 00,
897 X00 XX,



⚠ DANGER

- DE** Anschluss **ausschließlich** durch ausgebildete Elektro-Fachkräfte.
- GB** Electrical connection is to be made by trained electrical specialists **only**.
- FR** Le branchement doit **uniquement** être effectué par des professionnels.
- IT** Il collegamento deve essere eseguito **solo** da elettricisti specializzati.
- ES** La conexión **sólo** debe ser realizada por electricistas debidamente formados.
- PT** A ligação deve ser feita **exclusivamente** por profissional elétrico especializado.
- NL** De aansluiting mag **enkel** gebeuren door erkende vakmensen.
- CZ** Připojení smí **provádět** pouze kvalifikovaný personál.
- PL** Podłączenie **wyłącznie** przez specjalistów-elektryków.
- FI** Liittäminen kuuluu **ainoastaan** koulutettujen sähköalan ammattilaisten tehtäviin.
- RU** Подключение проводится только специа-листом-электриком.
- TR** Bağlantı **sadece** eğitimli elektrik teknisyenleri tarafından yapılmalıdır.
- CN** 布线需由专业电工执行



890 x00 00	
895 x00 00	12 V - 240 V ≈, ≤ 25 W, E27
890 x10 00	
895 x10 00	12 V - 240 V ≈, ≤ 2 x 15W, E14
897 x00 55	24 V ≈, ≤ 700 mA
897 x00 68	230 V~, ≤ 200 mA



955 890 38 | E14, 230 V ≈, 15 W



956 050 67 LED-Bulb, E27, 115 V~
956 050 68 LED-Bulb, E27, 230 V~
956 050 75 LED-Bulb; E27, 12-24 V~






897 x00 55 | T 1,25 A / 250 V ~



897 x00 68 | T 1,0 A / 250 V~



⚠ DANGER





4

890 + 


975 890 33
 975 890 34
 975 890 35
 975 890 37

4a






A



B

	A	B	A	B
	93 mm 3.66"	190 mm 7.48"	245 mm 9.65"	338 mm 13.31"
	251,2 mm 9.89"	348,2 mm 13.71 "	406,2 mm 15.87"	496,2 mm 19,54"
	409,4 mm 16.12"	506,4 mm 19.94 "	561,4 mm 22.10"	645,4 mm 25.76"
	567,6 mm 22.35 "	664,6 mm 26.17"	719,6 mm 28.33"	812,6 mm 31.99"


4b




4c



1.




2.




SW 24
2 Nm

! IP 65


5




1.



2.




3.




6

6a - 890 x00 00, 895 x00 00
 6b - 890 x10 00, 895 x10 00
 6c- 897


6a




1.



2.




3.




„clac“

6b




6c


A: (DC) 897 x00 55
 B: (AC) 897 x00 68



A




B




N L

7

890 x10 00, 895 x10 00



8



1.




2.




1


897




1.




2.




3.



4.



2



931089000101_AJ
310.890.001

© D **WERMA**