


# Home - Fischerelektronik - LA V 24

---

 [fischerelektronik.de/web\\_fischer/en\\_GB/VA/LAV2430024/datasheet.xhtml](http://fischerelektronik.de/web_fischer/en_GB/VA/LAV2430024/datasheet.xhtml)



Cooling aggregates>Cooling aggregates with axial fan

155 x 158 mm, with axial fan and air-flow chamber

## Features

---

|        |        |
|--------|--------|
| width: | 155 mm |
|--------|--------|

---

|         |        |
|---------|--------|
| height: | 158 mm |
|---------|--------|

---

|         |        |
|---------|--------|
| length: | 300 mm |
|---------|--------|

---

|                     |                   |
|---------------------|-------------------|
| thermal resistance: | 0.078 - 0.025 K/W |
|---------------------|-------------------|

---

|          |                                                                                                                                               |
|----------|-----------------------------------------------------------------------------------------------------------------------------------------------|
| surface: | <ul style="list-style-type: none"><li>• raw degreased aluminium (by the metre raw aluminium)</li><li>• mounting area(s) milled flat</li></ul> |
|----------|-----------------------------------------------------------------------------------------------------------------------------------------------|


---

|                                     |                                                                              |
|-------------------------------------|------------------------------------------------------------------------------|
| operating voltage of the fan motor: | <ul style="list-style-type: none"><li>• 24 V DC</li><li>• 230 V AC</li></ul> |
|-------------------------------------|------------------------------------------------------------------------------|

---

## Technical Drawing

---



## Fan

type: ebmpapst, ball bearing, with grid

dimensions:  $\varnothing 150 \times 38$  mm

tension: 24 V DC

power inout: 19 W

max. air volume: 420 m<sup>3</sup>/h

temperature range: -25°C... +72°C

speed: 3,350 min<sup>-1</sup>

noise level: 59 dB(A)

weight: 620 g

failure rate (L<sub>10</sub>): L<sub>10</sub> > 75,000 h (40°C)

type: ebmpapst, ball bearing, with grid

dimensions:  $\varnothing 150 \times 55$  mm

|                                  |                                   |
|----------------------------------|-----------------------------------|
| tension:                         | 230 V AC                          |
| power inout:                     | 47 W                              |
| max. air volume:                 | 380 m <sup>3</sup> /h             |
| temperature range:               | -30°C... +60°C                    |
| speed:                           | 2,700 min <sup>-1</sup>           |
| noise level:                     | 60 dB(A)                          |
| weight:                          | 1100 g                            |
| failure rate (L <sub>10</sub> ): | L <sub>10</sub> > 40,000 h (40°C) |

**Fischer Elektronik GmbH & Co. KG**  
DEUTSCHLAND • GERMANY • ALLEMAGNE

Nottebohmstraße 28  
58511 Lüdenscheid

Telefon +49 2351 435-0  
Telefax +49 2351 45754

info@fischerelektronik.de  
www.fischerelektronik.de