

Eaton Bussmann series low voltage NH Fuse, Live gripping lug, 500V, 80A, 120 kAIC, Combination fuse status indicator, Blade end connection, Class C gL/gG, Square-body with knife blade contact, Metal plated copper contact plate, Ceramic body

Product Name	Catalog Number
Eaton Bussmann series low voltage NH Fuse	80NHG000B
	Packing Unit
	Pack
	Case Pack
EAN	Quantity
5027590206143	3
5027590364034	60
Gross Weight	Length
0.392 kg	83 mm
8.205 kg	420 mm
Width	Height
78 mm	56 mm
180 mm	140 mm
Volume	ERP Name
362.544 cm ³	SAP-UNITY
10584 cm ³	SAP-UNITY
Product Length/Depth	Product Height
79 mm	51 mm
Product Width	Product Weight
21 mm	119.333 g



		Compliances	Certifications
		CE Marked	IEC 60269-1
defaultTaxonomyAttributeLabel	Do pobrania		
		DIN 43620	

Type

fuse

Special features

Live gripping lug

Application

- industrial
- Utilities, Solar, Wind

Amperage Rating

80 A

Fitted with:

Metal gripping lugs

Fuse size

NH000

Current type

AC

Breaking capacity

120 kA

Frequency rating - max

62 Hz

Frequency rating - min

45 Hz

Rated switching capacity

120 kA

Rated voltage AC

500 V

Class

Class gG/gL

Fuse type

Square body with knife blade contact

Contact material

Metal plated copper

Utilization category

gL/gG (cable protection/equipment protection)

Interrupt rating

120 kAIC

Fuse indicator

Combination fuse status indicator

Insulated metal gripping lugs (IMGL)

No

Connection

Blade end

Construction

NH000

Construction size

NH000

Fuse shape

Square body

Knife blade contacts

Voltage type

AC

Suitable for

Microswitch 170H0236

EBF Vertical fuse rail

EBV Vertical fuse switch-disconnectors

EBH Size 000 Horizontal fuse switch-disconnectors

Material

Ceramic body

Quantity

3

Voltage rating

500 V



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. Wszelkie
prawa zastrzeżone.

Eaton is a registered trademark.

All other trademarks are
property of their respective
owners.



Eaton.com/socialmedia