



GPL series GPL 12520



Valve Regulated Lead Acid Battery

Maintenance-Free Sealed Lead Acid Battery.

Absorbent Glass Mat (AGM) technology for efficient gas recombination of up to 99%.

General

Design for Standby Power Applications

【Design Life】

Up to 10 Years in Standby Service at 25°C

Eurobat (20°C) : >12 YEARS VERY LONG LIFE

【Operating Temperature Range】

Nominal Operating Temperature : 25°C (77°F)

Discharge : -15°C ~ 50°C (5°F~122°F)

Charge: -15°C ~ 40°C (5°F~104°F)

Storage: -15°C ~ 40°C (5°F~104°F)

【Float Charging Voltage】

13.5 ~ 13.8 VDC/Unit at 25°C (77°F)

【Equalization Charging Voltage】

14.4 ~ 15.0 VDC/Unit at 25°C (77°F)

【Self Discharge】


Less than 10% after 90 days, can be stored up to 6 months at 25°C (77°F);

Fully recharging is required before usage, and charged sooner if stored at high temperature than 25°C (77°F).

Specification

Design according with IEC 60896-21/22:2004

Nominal Voltage	12V (6 cells per unit)		
Nominal Capacity	52 Ah @20hr-rate to 1.75V per cell @25°C (77°F)		
Weight	Approx. 17.80 Kg (39.23 lbs)		
Maximum Discharge Current	500A (5sec)		
Internal Resistance	Approx. 5.1mΩ		
Short Circuit Current	1485A		
Maximum Charge Current	15.60A		
Terminal types	I2 thread lead alloy terminal to accept M6 bolt		
Terminal tightening torque	51.7±10.3 Kgf·cm / 44.9±9.0 Lbf·in / 5.10±1.0 N·m		
Container Material	PP (UL 94-HB) & Flame Retardant (94-V0) available upon request		
Dimensions	Length (L)	228.0±2.5 mm	8.98±0.10 inch
	Width (W)	138.4±1.5 mm	5.45±0.06 inch
	Container Height (h)	201.3±2.5 mm	7.93±0.10 inch
	Overall Height (H)	206.3±2.5 mm	8.12±0.10 inch



Constant Current Discharge Characteristics Unit: A (25°C, 77°F)

F.V/Time	5MIN	10MIN	15MIN	30MIN	60MIN	90MIN	2HR	3HR	5HR	8HR	10HR	20HR
1.60V	225	155	116	67.2	38.5	27.7	21.7	15.2	9.66	6.35	5.17	2.66
1.67V	208	144	110	64.7	38.1	27.4	21.4	15.0	9.57	6.31	5.15	2.65
1.70V	195	138	108	63.6	37.8	27.3	21.3	14.9	9.53	6.28	5.14	2.64
1.75V	177	128	103	61.2	37.0	26.7	20.7	14.7	9.44	6.17	5.08	2.60
1.80V	159	119	95.7	58.7	35.7	26.0	20.3	14.3	9.22	6.04	4.94	2.56
1.85V	142	110	89.3	55.6	33.3	24.8	19.0	13.5	8.71	5.74	4.69	2.43

Constant Power Discharge Characteristics Unit: W (25°C, 77°F)

F.V/Time	5MIN	10MIN	15MIN	30MIN	60MIN	90MIN	2HR	3HR	5HR	8HR	10HR	20HR
1.60V	2392	1684	1290	770	447	325	250	176	114	74.7	61.6	31.7
1.67V	2176	1589	1235	748	445	323	247	175	113	74.4	61.2	31.6
1.70V	2081	1540	1208	737	443	322	246	174	112	74.2	60.7	31.4
1.75V	1914	1449	1160	710	434	315	242	171	111	73.9	60.3	31.3
1.80V	1747	1359	1093	683	419	308	235	169	110	72.4	59.5	30.7
1.85V	1584	1258	1031	649	395	295	223	161	105	69.6	56.7	29.4

Please refer to the official site for the latest rating confirmation. URL: www.csb-battery.com

Issued: 200914

Sales Offices

希世比能源科技股份有限公司
CSB Energy Technology Co., Ltd.

BUSINESS HEADQUARTERS

Tel: +886-2-2880-5600

Fax: +886-2-2888-3300

USA OFFICE

Tel: +1-817-244-7777 / 1-(800)3-CSB-USA (272872)

Fax: +1-817-244-4445

SHENZHEN OFFICE (CHINA)

Tel: +86-755-8831-6488/6775/6075

Fax: +86-755-8831-6548

EUROPE (EMEA) OFFICE

Tel: +31(0)180-418-140

Fax: +31(0)180-418-327

SHANGHAI OFFICE (CHINA)

Tel: +86-21-5046-1622/0833/0094

Fax: +86-21-5046-1046

Recognized under UL 1989,
and certified by ISO 9001, 14001, 45001, 50001.



TAIPEI OFFICE

Tel: +886-2-2880-5600

Fax: +886-2-2888-3300

BEIJING OFFICE (CHINA)

Tel: +86-10-6597-8065/8165/8265

Fax: +86-10-6597-8565