


Home - Fischerelektronik - LA V 33

 fischerelektronik.de/web_fischer/en_GB/VA/LAV3320012/datasheet.xhtml



Cooling aggregates>Cooling aggregates with axial fan

244,2 x 85 mm, with axial fan and air-flow chamber

Features

width:	244.2 mm
--------	----------

height:	85 mm
---------	-------


length:	200 mm
---------	--------

thermal resistance:	0.027 - 0.061 K/W
---------------------	-------------------

surface:	raw degreased aluminium (by the metre raw aluminium)
----------	--

operating voltage of the fan motor:	• 12 V DC • 24 V DC • 48 V DC
-------------------------------------	---

Technical Drawing



Fan

type:	ebmpapst 8212 JH4
dimensions:	80x80x38 mm
tension:	12 V DC
power inout:	39 W
max. air volume:	222 m ³ /h
temperature range:	-20°C... +70°C
speed:	14,000 min ⁻¹
noise level:	71 dB(A)
weight:	200 g
failure rate (L ₁₀):	L ₁₀ > 50,000 h (40°C)

type:	ebmpapst 8214 JH4
dimensions:	80x80x38 mm
tension:	24 V DC

power inout:	38 W
max. air volume:	222 m ³ /h
temperature range:	-20°C... +70°C
speed:	14,000 min ⁻¹
noise level:	71 dB(A)
weight:	200 g
failure rate (L ₁₀):	L ₁₀ > 50,000 h (40°C)
type:	ebmpapst 8218 JH4
dimensions:	80x80x38 mm
tension:	48 V DC
power inout:	36 W
max. air volume:	222 m ³ /h
temperature range:	-20°C... +70°C
speed:	14,000 min ⁻¹
noise level:	71 dB(A)
weight:	200 g
failure rate (L ₁₀):	L ₁₀ > 50,000 h (40°C)