

to 6	$\pm 0,1$
above to 30	$\pm 0,2$
above to 100	$\pm 0,3$
above to 300	$\pm 0,5$
above to 1000	$\pm 0,8$
above to 2000	$\pm 1,2$
above to 4000	2
above 4000	3

All transfer to third person or missusage for unauthorized purposes is strictly forbidden by Author's Rights

C0_RAK001_0201

Technical drawing of a 12V 100Ah battery, showing front, top, and side views with dimensions and markings.

Front View:

- Overall height: 12 ± 1 mm (top section) and $67 \begin{smallmatrix} +2 \\ -1 \end{smallmatrix}$ mm (main body).
- Terminal height: $12 \begin{smallmatrix} +1 \\ 0 \end{smallmatrix}$ mm.
- Terminal thread: M8.
- Marking: A dashed rectangle indicates the location of the marking.

Top View:

- Overall diameter: $\varnothing 38 \pm 0,5$ mm.
- Terminal layout: Four terminals labeled 1, 2, 3, and 4, with a ground symbol (⊕) and a minus sign (-) also indicated.

Side View:

- Shows the battery's profile and the terminal connection point.

```
date:
week.year
```



material			protection		standard			issue			RRN 434/22	
changes	1	2	3	4	5	6	7	8	9	10	 Iskra [®] Iskra, d.o.o. PE Kondenzatorji	
request.												
date												
signature												
	date	signature	name EMI RFI Filter Class X1Y2 Type KPL3009 16A/40°C 275Vac 50/60 Hz								identification No.	
design.	28. 3. 11	Biličić A.									10203-06	
approved	28. 3. 11	Štravs B.									scale	
stand.	19. 9. 22	Plut D.									page	
											1 of 1	