

Home - Fischerelektronik - LA V 9

 fischerelektronik.de/web_fischer/en_GB/VA/LAV910024/datasheet.xhtml



Cooling aggregates>Cooling aggregates with axial fan

80 x 83 mm, with axial fan and air-flow chamber

Features

width:	80 mm
--------	-------

height:	83 mm
---------	-------


length:	100 mm
---------	--------

thermal resistance:	0.26 - 0.1 K/W
---------------------	----------------

surface:	• raw degreased aluminium (by the metre raw aluminium) • mounting area(s) milled flat
----------	---

operating voltage of the fan motor:	• 24 V DC • 230 V AC
-------------------------------------	--

Technical Drawing



Fan

type: ebmpapst 8556N

dimensions: 80x80x38 mm

tension: 230 V AC

power inout: 12 W

max. air volume: 50 m³/h

temperature range: -40°C... +90°C

speed: 2,800 min⁻¹

noise level: 31 dB(A)

weight: 490 g

failure rate (L₁₀): L₁₀ > 52,500 h (40°C)

type: ebmpapst 8314H

dimensions: 80x80x32 mm

tension: 24 V DC

power inout:	6 W
max. air volume:	80 m ³ /h
temperature range:	-20°C... 75°C
speed:	5,000 min ⁻¹
noise level:	48 dB(A)
weight:	170 g
failure rate (L ₁₀):	L ₁₀ > 55,000 h (40°C)

Fischer Elektronik GmbH & Co. KG
DEUTSCHLAND • GERMANY • ALLEMAGNE

Nottebohmstraße 28
58511 Lüdenscheid

Telefon +49 2351 435-0
Telefax +49 2351 45754

info@fischerelektronik.de
www.fischerelektronik.de