


KombiSIGN 71/72



**DANGER**



DE Anschluss **ausschließlich** durch ausgebildete Elektro-Fachkräfte.

GB Electrical connection is to be made by trained electrical specialists **only**.

FR Le branchement doit **uniquement** être effectué par des professionnels.

IT Il collegamento deve essere eseguito **solo** da elettricisti specializzati.

ES La conexión **sólo** debe ser realizada por electricistas debidamente formados.

PT A ligação deve ser feita **exclusivamente** por profissional elétrico especializado.

NL De aansluiting mag **enkel** gebeuren door erkende vakmensen.

CZ Připojení smí **provádět** pouze kvalifikovaný personál.

PL Podłączenie **wyłącznie** przez specjalistów-elektryków.

FI Liittäminen kuuluu **ainoastaan** koulutettujen sähköalan ammattilaisten tehtäviin.

RU Подключение проводится только специалистом-электриком.

TR Bağlantı **sadece** eğitimli elektrik teknisyenleri tarafından yapılmalıdır.

CN 布线需由专业电工执行

**DANGER**



DE Bei Epilepsie ungeeignet!

GB Unsuitable for epilepsy sufferers.

FR Ne convient pas aux personnes souffrant d'épilepsie.

IT Inadatto per epilettici.

ES Inadecuado para epilépticos.

PT Não aconselhavel a pessoas que sofrem de Epilepsia.

NL Niet geschikt voor epileptici.

CZ Nevhodné pro epileptiky.


PL Nie stosować przy zchorzeniu padaczkci.

FI Ei soveltu epileptikoille.

RU Не подходит для страдающих эпилепсией.

TR Epilepsi hastalığı olanların kullanmaması önerilir.

CN 不适用于癫痫病患者









Terminal element	640 xx0 00 640 812 01	12-230 V≈ 12-230 V≈	
TwinLIGHT	647 x10 75 647 x30 75	24 V≈ 24 V≈	< 80 mA < 80 mA
TwinFLASH	647 x20 55 647 x40 55	24 V≈ 24 V≈	< 80 mA < 80 mA
Multicolour	644 450 55	24 V≈	< 120 mA
LED	644 x00 75	24 V≈	< 35 mA
Permanent	644 x00 67 644 x00 68	115 V~ 230 V~	< 25 mA < 35 mA
LED RD	644 100 54	12 V≈	< 50 mA
Perm- GN	644 200 54	12 V≈	< 50 mA
anent YE	644 300 54	12 V≈	< 50 mA
LED	644 x10 75	24 V≈	< 30 mA
Blinking	644 x10 67 644 x10 68	115 V~ 230 V~	< 25 mA < 35 mA
LED Flash	644 x20 55	24 V≈	< 35 mA
LED	644 x30 75	24 V≈	< 40 mA
Rotating	644 x80 55	24 V≈	< 190 mA
LED Ultrabright	644 x40 55	24 V≈	< 350 mA
LED-EVS	644 x40 55	24 V≈	< 350 mA
Xenon	643 x00 54	12 V≈	195 mA
Flash	643 x00 55	24 V≈	125 mA
(2Ws)	643 x00 67 643 x00 68 643 x10 55	115 V~ 230 V~ 24 V≈	22 mA 15 mA < 125 mA
Permanent	641 x00 00	12-230 V≈	
	956 x00 75 956 x00 67 956 x00 68	24 V≈ 115 V~ 230 V~	< 45 mA < 15 mA < 15 mA

	955 840 34 955 840 35 955 840 38 955 840 57	12 V 24 V 230 V 115 V	5W 5W 5W 5W
	645 870 75 645 870 67 645 870 68 645 102 75	24 V≈ 115 V~ 230 V~ 24 V≈	< 40mA < 60mA < 60mA < 40mA
	645 800 75 645 800 77 645 800 68	24 V≈ 115 V~ 230 V~	< 25 mA < 35 mA < 35 mA
	645 x90 75 645 x90 60	24 V≈ 115-230 V~	< 30 mA < 45 mA
	645 850 55	24 V≈	< 80 mA
	645 810 55	24 V≈	< 150 mA
	645 840 55	24 V≈	< 400 mA
	645 860 55	24 V≈	< 400 mA
	645 830 55	24 V≈	< 100 mA












1

1a: 640 x00 00, 640 820 00
1b: 640 x00 00, 640 820 00 + 975 840 85, 960 000 52, 975 840 86
1c: 640 x10 00, 640 812 01, 640 830 00 + 975 840 10, 960 000 51, 975 840 90, 960 000 50, 975 840 91, ...
1d: 640 x00 00, 640 820 00 + 960 000 02, 960 000 53, 960 000 01, 960 000 54
1e: 940 000 41






Colour (RD)	24V		
Colour (GN)		24V	
Colour (YE)	24V	24V	
Colour (BU)			24V
Colour (WH)	24V	24V	24V
Colour (TQ)		24V	24V
Colour (VT)	24V		24V



		Pin terminal element				
	Tone	1	2	3	4	5
	1	+24V	+24V	NC		
	2	+24V	+24V	+24V		
	3	+24V	NC	NC		
	4	+24V	NC	+24V		
	5	NC	+24V	NC		
	6	NC	+24V	+24V		
	7	NC	NC	+24V		
	1		+24V	+24V	NC	
	2		+24V	+24V	+24V	
	3		+24V	NC	NC	
	4		+24V	NC	+24V	
	5		NC	+24V	NC	
	6		NC	+24V	+24V	
	7		NC	NC	+24V	
	1			+24V	+24V	NC
	2			+24V	+24V	+24V
	3			+24V	NC	NC
	4			+24V	NC	+24V
	5			NC	+24V	NC
	6			NC	+24V	+24V
	7			NC	NC	+24V
	1				+24V	+24V
	3				+24V	NC
	5				NC	+24V
	3					+24V



		Pin terminal element				
	Tone	1	2	3	4	5
	1		+24V	NC	NC	NC
	2		NC	+24V	NC	NC
	3		+24V	+24V	NC	NC
	4		NC	NC	+24V	NC
	5		+24V	NC	+24V	NC
	6		NC	+24V	+24V	NC
	7		+24V	+24V	+24V	NC
	8		NC	NC	NC	+24V
	9		+24V	NC	NC	+24V
	10		NC	+24V	NC	+24V
	11		+24V	+24V	NC	+24V
	12		NC	NC	+24V	+24V
	13		+24V	NC	+24V	+24V
	14		NC	+24V	+24V	+24V
	15		+24V	+24V	+24V	+24V
	1			+24V	NC	NC
	2			NC	+24V	NC
	3			+24V	+24V	NC
	4			NC	NC	+24V
	5			+24V	NC	+24V
	6			NC	+24V	+24V
	7			+24V	+24V	+24V
	1				+24V	NC
	2				NC	+24V
	3				+24V	+24V
	1				+24V	+24V