


FOR 客户名称	APPROVED 客户确认签字	ATTN 销售负责人



PART NUMBER: USB-12-△

"Δ"	CRUST COLOR
NO LETTER	SILVER
BK	BLACK
OTHER COLOR CAN BE CUSTOMIZED	

SPECIFICATIONS:

1. OPERATION TEMPERATURE: -25°C ~ +55°C (NO FREEZING) .
2. OPERATION HUMIDITY: 45 ~ 85%RH (NO CONDENSATION) .
3. TRANSMISSION RATE: ≥100MB/s.
4. HEAD PORT: USB3.0 A TYPE FEMALE.
5. BACK PORT: USB3.0 A TYPE MALE.

MATERIAL:

- 1.BODY: AL ALLOY.

BRAND 品牌		红波按钮制造有限公司 ONPOW PUSH BUTTON MANUFACTURE CO.,LTD.			
 欧宝龙®					
TITLE 名称 PANEL MOUNTING TYPE USB3.0 CONNECTOR					UNIT 单位 mm
DWG NO. 图号 USB-12		SCALE 比例 1.2 : 1		SIZE 图纸 A4	
FILE NAME 档案名称 金属转接线 USB3.0.DWG		DRAWN 制图 YDY 2022/07/01		SHEET 张 1/1 REV. 更改 1	