





FOR 客户名称	APPROVED 客户确认签字	ATTN 销售负责人



PART NUMBER:USBC-11-△

"△"	CRUST MATERIAL
NO LETTER	AL ALLOY(SILVER)
BK	AL ALLOY(BLACK)
OTHER COLOR CAN BE CUSTOMIZED	

SPECIFICATIONS:

1.OPERATING TEMPERATURE: -25℃~ +55℃(NO FREEZING, KEEP THE AIR FLOWING AROUND PUSHBUTTON).

2.OPERATION HUMIDITY: 45~ 85%RH(NO CONDENSATION).

3.FUNCTION: 5A FAST CHARGING,10GBps RATE.

4.APPLICATION:MP3/MP4 PLAYER,VIDEO GAME PLAYER, CAMERA AND MOBILE PHONE.

5.HEAD PORT: USB3.1 C TYPE FEMALE.

6.BACK PORT: USB3.0 A TYPE MALE.

7.TORQUE: 0.6Nm Max. APPLIED TO NUT.

8.GENERAL TOLERANCE:0-18mm=±0.25, 18-80mm=±0.52.

MATERIALS:

1.BODY: AL ALLOY.

BRAND 品牌		红波按钮制造有限公司			
ONPOW 欧宝龙®		ONPOW PUSH BUTTON MANUFACTURE CO.,LTD.			
TITLE 名称	PANEL MOUNTING TYPE USB3.1 CONNECTOR			UNIT 单位	mm
DWG NO. 图号	USBC-11			SCALE 比例	1 : 1
FILE NAME 档案名称	金属带线 USB3.1.DWG	DRAWN 制图	HCP 2023/12/14	SHEET 张	1/1
				REV. 更改	1