





- Robust test probes with distinctive collar (stop) on the barrel
- Optimum adjustment of the stroke ratios in the test fixture:
The collar is available in different heights, which, in combination with the receptacles, allows a range of installation heights
- Stainless steel versions for temperatures from -100 °C up to +200 °C available



General data

Product group:	ICT / FCT (in-circuit test and function test)
Sub-product group:	Metric standard
Series:	GKS-112
Grid:	2.54 mm [100 mil]
Contacting from:	Pad, pin
Magnetic:	Yes
Installation type:	Plug-in
Quick-exchange system:	Yes
Adjustable installation height:	No
Non-rotating:	No
Compatible receptacle(s):	KS-112
Min. temperature:	- 40 °C [- 104 °F]
Max. temperature:	+ 80 °C [+ 176 °F]
RoHS-compliant:	RoHS-3;6a;6c

Electrical data

Current load capacity / rated current:	5 A
Typical resistance (Ri):	<20 mOhm

Mechanical data

Total length:	34.3 mm [1.35 in]
Barrel diameter:	1.66 mm [0.065 in]
Maximum stroke:	5.3 mm [0.208 in]
Spring pre-load:	1.49 N [5.35 ozf]
Collar height:	04
Spring force at working stroke:	5 N [17.9 ozf]
Recommended working stroke:	4 mm [0.157 in]

Tip style data

Tip style:	09 flexi-needle, self-cleaning
Tip diameter:	0.6 mm [0.023 in]
Tip style surface:	N nickel
Tip style material:	2 steel

Test Probe


GKS-112 209 060 N 5004

Item GKS-112-1036



ingun[®]

Partner for Future Technology



INGUN Prüfmittelbau GmbH

Max-Stromeyer-Straße 162
78467, Constance, Germany
Phone +49 7531 8105-0
Customer hotline +49 7531 8105-888
Fax +49 7531 8105-65
info@ingun.com



Prices and delivery times on request.

Learn more about
ICT/FCT Test probes



ICT/FCT TEST PROBES

ingun.com