

Home - Fischerelektronik - LA V 17

 fischerelektronik.de/web_fischer/en_GB/VA/LAV1710024/datasheet.xhtml



Cooling aggregates>Cooling aggregates with axial fan

122 x 120 mm, with axial fan and air-flow chamber

Features

width: 122 mm

height: 120 mm

length: 100 mm

thermal resistance: 0.092 - 0.046 K/W


surface:

- raw degreased aluminium (by the metre raw aluminium)
- mounting area(s) milled flat

operating voltage of the fan motor:

- 24 V DC
- 230 V AC

Technical Drawing



Fan

type: ebmpapst 4184NXH

dimensions: 119x119x38 mm

tension:	24 V DC
power inout:	11 W
max. air volume:	237 m ³ /h
temperature range:	-30°C ... +70°C
speed:	4,400 min ⁻¹
noise level:	57 dB(A)
weight:	390 g
failure rate (L ₁₀):	L ₁₀ > 70,000 h (40°C)
type:	ebmpapst 4656N
dimensions:	119x119x38 mm
tension:	230 V AC
power inout:	19 W
max. air volume:	160 m ³ /h
temperature range:	-40°C... +85°C
speed:	2,650 min ⁻¹
noise level:	47 dB(A)
weight:	550 g
failure rate (L ₁₀):	L ₁₀ > 37,500 h (40°C)