



Cooling aggregates>Cooling aggregates with axial fan

93 x 184 mm, with axial fan and air-flow chamber

Features

width:	184 mm
--------	--------

height:	93 mm
---------	-------



length:	200 mm
---------	--------

thermal resistance:	0.098 - 0.046 K/W
---------------------	-------------------

surface:	raw degreased aluminium (by the metre raw aluminium)
----------	--

operating voltage of the fan motor:	• 24 V DC • 230 V AC
-------------------------------------	--

Technical Drawing



Fan

type: ebmpapst 3314 NHH

dimensions: 92x92x32 mm

tension: 24 V DC

power inout: 3.4 W

max. air volume: 107 m³/h

temperature range: -20°C... 75°C

speed: 3,450 min⁻¹

noise level: 42 dB(A)

weight: 190 g

failure rate (L₁₀): L₁₀ > 57,500 h (40°C)

type:	ebmpapst 3656
dimensions:	92x92x38 mm
tension:	230 V AC
power inout:	12 W
max. air volume:	75 m ³ /h
temperature range:	-40°C... +75°C
speed:	2,700 min ⁻¹
noise level:	37 dB(A)
weight:	420 g
failure rate (L ₁₀):	L ₁₀ > 52,500 h (40°C)

Fischer Elektronik GmbH & Co. KG
 DEUTSCHLAND • GERMANY • ALLEMAGNE

Nottebohmstraße 28
 58511 Lüdenscheid

Telefon +49 2351 435-0
 Telefax +49 2351 45754

info@fischerelektronik.de
 www.fischerelektronik.de