


Home - Fischerelektronik - LA V 30

 fischerelektronik.de/web_fischer/en_GB/VA/LAV3020012/datasheet.xhtml



Cooling aggregates>Cooling aggregates with axial fan

190 x 65 mm, with axial fan and air-flow chamber

Features

width:	190 mm
--------	--------

height:	65 mm
---------	-------


length:	200 mm
---------	--------

thermal resistance:	0.03 - 0.07 K/W
---------------------	-----------------

surface:	raw degreased aluminium (by the metre raw aluminium)
----------	--

operating voltage of the fan motor:	• 12 V DC • 24 V DC • 48 V DC
-------------------------------------	---

Technical Drawing



Fan

type:	ebmpapst 612 JH
dimensions:	60x60x32 mm
tension:	12 V DC
power inout:	7.7 W
max. air volume:	70 m ³ /h
temperature range:	-20°C... +70°C
speed:	11,700 min ⁻¹
noise level:	53 dB(A)
weight:	100 g
failure rate (L ₁₀):	L ₁₀ > 57,500 h (40°C)

type:	ebmpapst 614 J/2HHP
dimensions:	60x60x32 mm
tension:	24 V DC

power inout:	14.6 W
max. air volume:	82 m ³ /h
temperature range:	-20°C... 75°C
speed:	15,000 min ⁻¹
noise level:	62 dB(A)
weight:	100 g
failure rate (L ₁₀):	L ₁₀ > 65,000 h (40°C)
type:	ebmpapst 618 J/2HHP
dimensions:	60x60x32 mm
tension:	48 V DC
power inout:	14.6 W
max. air volume:	82 m ³ /h
temperature range:	-20°C... 75°C
speed:	15,000 min ⁻¹
noise level:	62 dB(A)
weight:	100 g
failure rate (L ₁₀):	L ₁₀ > 65,000 h (40°C)