






GO TO PRODUCT

- Robust test probes with distinctive collar (stop) on the barrel
- Optimum adjustment of the stroke ratios in the test fixture:
The collar is available in different heights, which, in combination with the receptacles, allows a range of installation heights
- Stainless steel versions for temperatures from -100 °C up to +200 °C available



1:1



General data

Product group:
Sub-product group:
Series:
Grid:
Contacting from:
Magnetic:
Installation type:
Quick-exchange system:
Adjustable installation height:
Non-rotating:
Compatible receptacle(s):
Min. temperature:
Max. temperature:
RoHS-compliant:

ICT / FCT (in-circuit test and function test)
Metric standard
GKS-113
4 mm [157 mil]
Pad
Yes
Plug-in
Yes
No
KS-113, KS-113 23
- 40 °C [- 104 °F]
+ 80 °C [+ 176 °F]
RoHS-3;6a;6c

Electrical data

Current load capacity / rated current:
Typical resistance (Ri):

5 A
<30 mOhm

Mechanical data

Total length: 35.3 mm [1.38 in]
Barrel diameter: 2.65 mm [.104 in]
Maximum stroke: 5.3 mm [.208 in]
Spring pre-load: 0.21 N [.755 ozf]
Collar height: 10
Spring force at working stroke: 0.6 N [2.15 ozf]
Recommended working stroke: 4 mm [.157 in]

Tip style data

Tip style: 01 30° needle tip, self-cleaning
Tip diameter: 1.8 mm [.070 in]
Tip style surface: R rhodium
Tip style material: 2 steel

Test Probe


GKS-113 201 180 R 0610

Item GKS-113-0539



ingun[®]

Partner for Future Technology



INGUN Prüfmittelbau GmbH

Max-Stromeyer-Straße 162
78467, Constance, Germany
Phone +49 7531 8105-0
Customer hotline +49 7531 8105-888
Fax +49 7531 8105-65
info@ingun.com



Prices and delivery times on request.
Technical changes reserved. 03/24_GB

Learn more about
ICT/FCT Test probes



ingun.com