

Home - Fischerelektronik - LA V 31

 fischerelektronik.de/web_fischer/en_GB/VA/LAV3130012/datasheet.xhtml



Cooling aggregates>Cooling aggregates with axial fan

85 x 85 mm, with axial fan and air-flow chamber


High performance cooling aggregate

- additional efficiency enhancement and noise reduction by means of air-technically adjusted airflow chambers
- excellent thermal efficiency in connection with powerful axial fans
- double-sided precise milled semiconductor mounting surfaces
- different width dimensions, customised machinings, surfaces, fan types and fan voltages upon request

Features

width:	85 mm
height:	85 mm
length:	300 mm
thermal resistance:	0.052 - 0.144 K/W
surface:	raw degreased aluminium (by the metre raw aluminium)
operating voltage of the fan motor:	• 12 V DC • 24 V DC • 48 V DC

Technical Drawing



Fan

type: ebmpapst 8212 JH4

dimensions: 80x80x38 mm

tension: 12 V DC

power inout: 39 W

max. air volume: 222 m³/h

temperature range: -20°C... +70°C

speed: 14,000 min⁻¹

noise level: 71 dB(A)

weight: 200 g

failure rate (L₁₀): L₁₀ > 50,000 h (40°C)

type: ebmpapst 8214 JH4

dimensions: 80x80x38 mm

tension:	24 V DC
power inout:	38 W
max. air volume:	222 m ³ /h
temperature range:	-20°C... +70°C
speed:	14,000 min ⁻¹
noise level:	71 dB(A)
weight:	200 g
failure rate (L ₁₀):	L ₁₀ > 50,000 h (40°C)
type:	ebmpapst 8218 JH4
dimensions:	80x80x38 mm
tension:	48 V DC
power inout:	36 W
max. air volume:	222 m ³ /h
temperature range:	-20°C... +70°C
speed:	14,000 min ⁻¹
noise level:	71 dB(A)
weight:	200 g
failure rate (L ₁₀):	L ₁₀ > 50,000 h (40°C)