

# Spring-loaded test probe GKS-112 302 200 A 3002

Item GKS-112-0260





GO TO PRODUCT

**ingun**<sup>®</sup>

Partner for Future Technology

- Robust test probes with distinctive collar (stop) on the barrel
- Optimum adjustment of the stroke ratios in the test fixture:  
The collar is available in different heights, which, in combination with the receptacles, allows a range of installation heights
- Stainless steel versions for temperatures from -100 °C up to +200 °C available



## General data

|                                 |                                               |
|---------------------------------|-----------------------------------------------|
| Product group:                  | ICT / FCT (in-circuit test and function test) |
| Sub-product group:              | Metric standard                               |
| Series:                         | GKS-112                                       |
| Grid:                           | 2.54 mm [100 mil]                             |
| Contacting from:                | Pin, Pfosten, Bead, Flachkontakt              |
| Magnetic:                       | Yes                                           |
| Installation type:              | Plug-in                                       |
| Quick-exchange system:          | Yes                                           |
| Adjustable installation height: | No                                            |
| Non-rotating:                   | No                                            |
| Compatible receptacle(s):       | KS-112                                        |
| Min. temperature:               | - 40 °C [- 104 °F]                            |
| Max. temperature:               | + 80 °C [+ 176 °F]                            |
| RoHS-compliant:                 | RoHS-3;6c                                     |

## Electrical data

|                                        |          |
|----------------------------------------|----------|
| Current load capacity / rated current: | 8 A      |
| Typical resistance (Ri):               | <20 mOhm |

## Mechanical data

|                                 |                    |
|---------------------------------|--------------------|
| Total length:                   | 32.3 mm [1.27 in]  |
| Barrel diameter:                | 1.66 mm [0.065 in] |
| Maximum stroke:                 | 5.3 mm [0.208 in]  |
| Spring pre-load:                | 0.6 N [2.15 ozf]   |
| Collar height:                  | 02                 |
| Spring force at working stroke: | 3 N [10.7 ozf]     |
| Recommended working stroke:     | 4 mm [0.157 in]    |

## Tip style data

|                     |                 |
|---------------------|-----------------|
| Tip style:          | 02 flat         |
| Tip diameter:       | 2 mm [0.078 in] |
| Tip style surface:  | A gold          |
| Tip style material: | 3 CuBe          |


# Spring-loaded test probe GKS-112 302 200 A 3002

Item GKS-112-0260



**ingun**<sup>®</sup>

Partner for Future Technology



## INGUN Prüfmittelbau GmbH

Max-Stromeyer-Straße 162  
78467, Constance, Germany  
Phone +49 7531 8105-0  
Customer hotline +49 7531 8105-888  
Fax +49 7531 8105-65  
info@ingun.com



Prices and delivery times on request.  
Technical changes reserved. 02/24\_GB

Learn more about  
ICT/FCT Test probes



[ingun.com](https://www.ingun.com)

ICT/FCT TEST PROBES