

Radio-frequency probe

HFS-840 307 100 A 9202V236S4M

Item HFS-840-0623



GO TO PRODUCT

ingun[®]

Partner for Future Technology

- Long standard series
- Up to 4 GHz
- Cable interface MCX
- Screw-in version of asymmetrical probes, with additional crimp point to secure positioning
- Receptacles: KS-810 M5-R, KS-810 M5-F

General data

Product group:	HFS radio-frequency test probes
Series:	HFS-840
Sub-series:	HFS-840 4M screw-in with adjustable positioning
Grid:	5.8 mm [228 mil]
DUT / contact:	PCB pad GGSGG
Installation type:	Screw-in
Floating mount:	No
Non-rotating:	Yes
Continuous plunger:	Yes
Interface of compatible assembly:	MCX 50 Ohm
Compatible assembly interface gender:	M signal conductor male / pin
KS sub-series:	KS-810 M, screw-in version
Min. temperature:	- 40 °C [- 104 °F]
Max. temperature:	+ 80 °C [+ 176 °F]
RoHS-compliant:	RoHS-3;6a;6c

Outer conductor data

Outer conductor tip style:	01 30° needle tip, self-cleaning
Outer conductor tip style diameter:	4 mm [.157 in]
Spring force of entire outer conductor at working stroke:	9.2 N [33.0 ozf]
Outer conductor working stroke:	5 mm [.196 in]
Outer conductor maximum stroke:	6.5 mm [.255 in]
Exchangeable outer conductor:	KO-810-0065
Outer conductor max. current load capacity:	3 A

Inner conductor data

Inner conductor tip style:	07 90° 3-edged chisel, self-cleaning
Inner conductor tip style diameter:	1 mm [.039 in]
Inner conductor tip style material:	3 CuBe
Inner conductor tip style surface:	A gold
Number of inner conductors:	1
Exchangeable inner conductor:	UKS-051307100A
Inner conductor working stroke:	0 mm [0 in]
Spring force of each inner conductor at working stroke:	0 N [0 ozf]
Inner conductor maximum stroke:	0 mm [0 in]
Inner conductor max. current load capacity:	3 A

Electrical data

Frequency range up to:	4 GHz
Impedance:	50 Ohm
Dielectric strength:	1.1 kV

Mechanical data

Total spring force at working stroke:	9.2 N [33.0 ozf]
Total length:	44 mm [1.73 in]
Barrel diameter:	4.5 mm [.177 in]
Installation height without receptacle:	12.5 mm [.492 in]
Torque in receptacle:	10 - 20 cNm [.885 - 1.77 lbf·in]

INGUN Prüfmittelbau GmbH

Max-Stromeyer-Straße 162
78467, Constance, Germany
Phone +49 7531 8105-0
Customer hotline +49 7531 8105-888
Fax +49 7531 8105-65
info@ingun.com



Prices and delivery times on request.
Technical changes reserved. 04/24_GB

Learn more about
Radio-frequency test probes



ingun.com

PCB