

Step probe

T-097 305 080 260 130A1102MO-G


Item T-097-0003



GO TO PRODUCT

ingun[®]

Partner for Future Technology



General data

Product group:	Screw-in test probe
Sub-product group:	Step probes
Series:	T-097 MO screw-in
Grid:	1.6 mm [62.9 mil]
Contacting from:	Pad, Female connector
Magnetic:	Yes
Installation type:	Screw-in
Quick-exchange system:	Yes
Adjustable installation height:	No
Non-rotating:	No
Screw-in torque:	0.5 - 1 cNm [.044 - .088 lbf-in]
Compatible receptacle(s):	KS-097 MO
Min. temperature:	- 40 °C [- 104 °F]
Max. temperature:	+ 80 °C [+ 176 °F]
RoHS-compliant:	RoHS-3;6c

Electrical data

Current load capacity / rated current:	3 A
Typical resistance (RI):	<50 mOhm

Mechanical data

Total length:	30.5 mm [1.20 in]
Barrel diameter:	0.66 mm [.025 in]
Maximum stroke:	5 mm [.196 in]
Spring pre-load:	0.39 N [1.40 ozf]
Collar height:	02
Spring force at working stroke:	1.1 N [3.95 ozf]
Recommended working stroke:	4 mm [.157 in]

Tip style data

Tip style:	05 bullet-nosed (full radius)
Tip diameter:	0.8 mm [.031 in]
Tip style surface:	A gold
Tip style material:	3 CuBe
Step probe tip height:	2.6 mm [.102 in]
Disk diameter:	1.3 mm [.051 in]

SCREW-IN TEST PROBE

Step probe


T-097 305 080 260 130A1102MO-G

Item T-097-0003



ingun[®]

Partner for Future Technology



INGUN Prüfmittelbau GmbH

Max-Stromeyer-Straße 162
78467, Constance, Germany
Phone +49 7531 8105-0
Customer hotline +49 7531 8105-888
Fax +49 7531 8105-65
info@ingun.com



Prices and delivery times on request.
Technical changes reserved. 04/24_GB

Learn more about
Screw-in test probe



SCREW-IN TEST PROBE

ingun.com